





SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	11	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	11		


CWS STATUS					REVISION HISTORY				AUTH	DR	APVD	APVD
DATE	STG	REV	N/P	CHG	ZONE							
16DE10	R	01	-	-		ALL PARTS CREATED PART DRAWING 13861584 WAS 13737728, REVISED & RELEASED 13861585 WAS 13737729, REVISED & RELEASED 13861586 WAS 13766034, REVISED & RELEASED			412702	LLJ	LLJ	JN
10FE11	R	02	-	-		ALL PARTS - CPA WAS 13831312			413296	JRL	JRL	JN
19JA18	R	03	-	-		ADDED "SHT1 OF 2" ALL PARTS - ADDED "ADDITIONAL INFO" NOTE & TERMINAL CONFIGURATION MOVED TO SHT 2			438575	ABC	ABC	MNC






TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101



SECTION A - A

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.

3. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.

4. FOR ADDITIONAL CABLE AND COMPONENTS INFORMATION SEE SHT 2.

		N/A		PROCESS SENSITIVE DIMENSION	
		DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)					
FROM	> 0	> 20	> 30	> 100	> 150
	> 20	> 30	> 70	> 100	> 200
	> 30	> 70	> 100	> 150	> 250
	> 70	> 100	> 150	> 200	> 300
	> 100	> 150	> 200	> 250	> 400
TOLERANCE UNLESS OTHERWISE SPECIFIED					
	±0.15	±0.2	±0.3	±0.4	±0.5
	±0.6	±0.8	±1	±1.2	
ANGULAR TOLERANCE 12°					