









15497352	02	AD	-	103	19.0	8.01	9.5 ±0.2	8.192
12146810	06	AK	-	102	8.0 - 5.0	6.06/4.32	4.8	7.751
12146809	06	AH	-	101	19.0 - 13.0	8.01/6.63	6.3 ±0.5	8.270
12146808	06	AJ	-	101	8.0 - 5.0	6.06/4.32	4.58	8.243
PART NO	REV	N/P	STATUS	TYPE	SIZE MM²	OD MM	Ø A	VOL CM³
CABLE								

SYMBOL DEFINITION			MISSING NUMBERS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	19		
	LAST NO. USED	22		

DWG STATUS					ZONE		REVISION HISTORY		AUTH	DR	APVD1	APVD2
DATE	STG	REV	N/P	CHG								
21DE00	R	01	-	-			ALL PARTS - REDRAWN TO PD, ADDED RIBS & REVISED HOLE CONSTRUCTION		202963	JLZ	RCH	RC
21DE00	R	02	-	-			12146809 - UPDATED PDM ATTRIBUTES; 12146808 & 12146810 - R 0.75 WAS 1.25		204828	RCH	RCH	RC
21DE00	R	03	-	-			ALL PARTS - REVISED HOLE CONSTRUCTION		205320	RCH	RCH	RC
12SE01	R	04	-	-			ALL PARTS - UPDATED PDM ATTRIBUTES		211668	RCH	RCH	LA
13DE01	R	05	-	-			PROCESS SENSITIVE DIMENSION 9 WAS 2		218574	OGG	GEG	AL
21MY03	R	06	-	-			12146808,10 - REVISED CABLE OD DIM		241451	LFS	RVP	MG
15JN04	-	07	-	-			15497352 - ADDED TO TAXI AND RELEASED		255553	AKJ	AKJ	GER
30JN04	R	08	-	-			15497352 - DIM "A" WAS 7.88		256394	ADK	ADK	GR
04NO04	R	09	-	-			ALL PARTS - 17.5 +/-0.2 WAS 17.5 15497352 - 9.5 +/-0.2 WAS 9.5		260973	EES	EES	GR
13DE05	R	10	-	-			12146810 - ADDED DETAIL A : DIMENSION A WAS 4.58		275635	MAC	MAC	JS
10OC06	R	11	-	-			ALL PARTS - REVISED MAT'L SPEC		285237	RTV	AMG	JAS
08DE06	R	12	-	-			ALL PARTS - Ø 16 +0.5/-0.3 WAS Ø 16		287319	MM	MM	JAS
06NO07	R	13	-	-			ALL PARTS - ADDED NOTE #4 WALL THICKNESS		402835	MM	MM	MDM



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
RING TERMINAL 12146363
- PART SURFACE MUST BE SMOOTH AND NONPOROUS.
- WALL THICKNESS TO BE 2.5 +0.2/-0.3 CONSTANT; UNLESS OTHERWISE NOTED.

9 PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART C
FROM TO	>0 >25 >60 >80 >80
TOLERANCE UNLESS OTHERWISE SPECIFIED	±0.3 ±0.5 ±0.6 ±0.75%
ANGULAR TOLERANCE	±2°

DWG TYPE PART DRAWING	
STYLE	
VOLUME (CM³)	SEE CHART
DISTR CODE	D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2001 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	USE MATH DATA

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH	
DR	DATE
APVD1 J. ZAMUDIO	21DE00
APVD2 R. CHACON	21DE00
APVD3 R. CORZAS	22DE00
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL M4523002	
DRAWING NAME TAXI SLEV BOOT	
DRAWING NUMBER 12146811	
SIZE A1	SCALE 2:1
FRAME NO 1 OF 1	SHEET NO 1 OF 1
STG R	REV 13
N/P	-