

● THESE DIMENSIONS ARE CRITICAL TO THE MECHANICAL AND ELECTRICAL PERFORMANCE OF THE CONNECTION SYSTEM.

MATERIAL SPECIFICATIONS

RECOMMENDED

BASE METAL - CDA-210, EXTRA SPRING TEMPER

- TIN PLATING - WHERE APPLICABLE TO 125°C MAX CONTINUOUS USAGE:: 0.005±0.0025 MM (200±100 µIN) ELECTROPLATED TIN.
- USAGE OF PLATING TYPES OTHER THAN RECOMMENDED MUST BE APPROVED BY DELPHI PACKARD ELECTRIC SYSTEMS ENGINEERING.

MINIMUMS

ELECTRICAL CONDUCTIVITY - 28% IACS AT 20 °C. USE OF A MATERIAL WITH CONDUCTIVITY <28% IACS MUST BE APPROVED BY PACKARD ELECTRIC MATERIALS ENGINEERING.

TENSILE STRENGTH - 430 - 480 MPa

UNDERPLATING FOR TIN PLATING - FOR BASE MATERIALS CONTAINING 10% OR MORE ZINC, AN UNDERPLATE OF COPPER 0.0025 MM (100 µIN) MINIMUM THICK IS REQUIRED.

PROCESSING LUBRICANT - ANY PROCESSING LUBRICANT REMAINING ON TERMINALS MUST BE COMPATIBLE WITH THE APPLICABLE PLATING SYSTEM. NON-PROCESSING LUBRICANTS MUST BE APPROVED TO A MAXIMUM TEMPERATURE OF 150°C. PROCESSING LUBRICANTS MUST BE APPROVED BY DELPHI PACKARD ELECTRIC SYSTEMS ENGINEERING.

MATING BLADE INFORMATION





NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
   DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA. ALL RADII 0.4
   DRAFT IS 1° ON ALL OUTSIDE SURFACES
2. THE SHAPE OF THE SHROUD AND LOCK ARE REPRESENTATIVE. OTHER SHAPES MAY BE USED AS LONG AS MATING SURFACES AND/OR MOLDING METHODS ARE PERMITTED AS LONG AS FUNCTION IS MAINTAINED
3. WHEN USING THIS INFORMATION FOR A NEW DESIGN, REQUEST THE LATEST COPY OF THIS PRINT FROM PACKARD ELECTRIC DIVISION.

MATING CONNECTOR INFORMATION OTHER APPLICATIONS











MATING CONNECTOR INFORMATION-ABS VI

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
   DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA. ALL RADII 0.4
   DRAFT IS 1° ON ALL OUTSIDE SURFACES
2. RECOMMENDED MAT'L - GLASS FILLED NYLON OR POLYESTER
3. WHEN USING THIS INFORMATION FOR A NEW DESIGN, REQUEST THE LATEST COPY OF THIS PRINT FROM PACKARD ELECTRIC DIVISION.

SYMBOL DEFINITION		MISSING SYMBOLS
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL (INI) DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED: 1	N2 MISSING SYMBOL NUMBER
	LAST NO. USED: 1	

DIMS STATUS	REV	SHT	ZONE	REVISION HISTORY	AUTH	DR	ENGR
12PSYM	R	51	-	12110293 - W/O SEPARATE DWG	15342	MEJ	JM JP
12PSYM	R	52	-	15324589 - RELEASED	990205	MEJ	JM JP
11JAN2	R	53	-	ALL PARTS - ADDED OPTIONAL CONSTRUCTION	24229	JGS	JGS MC
23APR7	R	54	-	ALL PARTS - UPDATED DRAWING TO LATEST STANDARDS & CHANGED TO L, FROM DIM 1	40668	EDS	MB DKS
14OCT1	R	55	-	ALL PARTS - ADDED ADHESIVE & APPLICATION DRAWING NOTES, 13FEB12 - RELEASED	41572	MEB	MB DKF
09NOV1	R	56	-	ALL PARTS - DIM 9.2 #6.8, 7, DIM A,B #45 6.1 #6 UPDATED LABEL INFO FIND PLACES!	43735	JAR	JAR JJS







OPTIONAL CONSTRUCTION





NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
   DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. WHEN PARTS ARE SHIPPED THEY MUST BE PACKED IN PLASTIC BAGS OR LINERS AND THE BAGS OR LINERS MUST BE SEALED TO AVOID ENTRY. BAGS OR LINERS MUST BE SEALED TO AVOID ENTRY OF FOREIGN MATTER.
3. DESIGN WILL PASS SALT FOG AND IMMERSION TEST AFTER CONDITIONING AS SPECIFIED IN EIA-710 (METRI-PACK).
   - WHEN MATED TO MATING PART OF EQUIVALENT.
4. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
5. FOR PART NUMBER WITH ADHESIVE, USE M/S1000) OR ADHESIVE APPROVED BY MATERIALS ENGINEERING TO SEAL CONNECTOR SEAL TO CONNECTOR.

			15324589	01	AD	15245588	12009842
12016670	01	AA	12110293	011		12110704	12052840
PART NO WITH ADHESIVE	REV	N/P	PART NO WITHOUT ADHESIVE	REV	N/P	CONNECTOR	SEAL CONN

| PUBLISHED RANGE (PR) | | | | | | |