









SECTION B-B



SECTION C-C



- ## NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. RECOMMENDED MATING BLADE THICKNESS 0.6±0.03 MM OR 0.64±0.03 MM
RECOMMENDED MATING BLADE WIDTH NOT TO EXCEED 1.2 MM
AND NO LESS THAN 0.61 MM.
3. MAXIMUM CURRENT CAPACITY IS 10 AMPS WITH 0.8 MM² COPPER CABLE.
4. CRIMP DIMENSION FROM THE BACK OF THE CORE WING (INCLUDES THE
FLARE OUT FROM THE CORE WING) TO THE END OF THE INSULATION WING

2.05 MM MAX WIDTH, 2.1 MM MAX HEIGHT FOR CABLE SIZE UP TO 1.9 MM O.D.
2.35 MM MAX WIDTH, 2.40 MM MAX HEIGHT FOR CABLE SIZE BETWEEN 1.86 TO 2.25 MM O.D.
2.67 MM MAX WIDTH, 2.67 MM MAX HEIGHT FOR CABLE SIZE BETWEEN 2.25 TO 2.40 MM O.D.

5. * DENOTES DIMENSIONS MADE AT CUT-OFF & CRIMP DIE.

6. PLUS ANGLE IS WING BOTTOM SURFACE ROTATED COUNTERCLOCKWISE AGAINST THE BOX BOTTOM SURFACE.

3		PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART D	
FROM	0		
TO	12	>12	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
	±0.1	±0.2	
ANGULAR TOLERANCE ±2°			

LINE DRAWING THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING. CONTACT APPLIED SALES TO ASSURE AVAILABILITY OF PARTS.	
UNO TYPE	
PART DRAWING	
STYLE	
VOLUME (CM)	DISTR CODE
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-2009, 9E. SEE APPLIED ENGINEERING DESIGN STANDARD BE 2017 FOR ISO 1101:2004 RECONSTRUCTION REQUIREMENTS.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	

● APTIV ● CONNECTION SYSTEMS WARREN, OH COPYRIGHT 2019 APTIV. ALL RIGHTS RESERVED. THIS DOCUMENT IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD/PLM DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
	DATE
DR	
APW01 LUIS VILLARREAL	28FE19
APW02 ROBERT B SNADER	01MR19
APW03 ROBERT B SNADER	01MR19
APW04	
APW05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV (03/04/2010)	
MATERIAL SEE CHART	
[DRAWING NAME]	