





SYMBOL DEFINITION			MISSING SYMBOLS		DWG STATUS				ZONE		REVISION HISTORY		AUTH	DR	APVD 1	APVD 2
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.			TOTAL NO OF INSPECTIONS REQUIRED	9	NO MISSING SYMBOL NUMBER		DATE	STG	REV	N/P	CHG	RELEASED	227916	RH	RH	FR
			LAST NO. USED	9			16JL02	R	01	-	-		229268	RVP	RVP	FR
							13AU02	R	01	AA	-	REVISED FIR TREE ORIENTATION	232652	RCH	RCH	FR
							290C02	R	01	AB	-	REVISED MAT'L SPEC	232652	RCH	RCH	FR
							21DE10	R	01	AC	-	B +0.15/-0.43 WAS B AND UPDATED MAT'L CALLOUT	412931	AJP	JAA	JPZ

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.
- (2.3)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED" OR NO LOGO.
- THIS PART TO SNAP INTO 6.35 DIA IN 5 MAX THICK STOCK.

3 PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	

DIMENSIONAL RANGE (MM)												CHART E1	
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300				
TO	20	30	70	100	150	200	250	300	400				
TOLERANCE UNLESS OTHERWISE SPECIFIED													
±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2													
ANGULAR TOLERANCE ±2°													

DWG TYPE		PART DRAWING			
STYLE					
VOLUME (QNP)		DISTR CODE			
2.256		D			
UNLESS OTHERWISE SPECIFIED					
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 0M GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE. ALL DIMENSIONS ARE IN MILLIMETERS					
REFERENCE					
THIRD ANGLE PROJECTION		DO NOT SCALE			
		USE MATH DATA			
					

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH	
DR	DATE
APVD1 R. HERMOSILLO	16JL02
APVD2 R. HERMOSILLO	16JL02
APVD3 F. ROMERO	17JL02
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL POLYPROPYLENE COMPOUND NATURAL	
DRAWING NAME MOUN CLIP TAPE ON SPECIAL	
DRAWING NUMBER 15429587	
SIZE A1	SCALE 2:1
FRAME NO 1 OF 1	SHEET NO 1 OF 1
STG R	REV 01
N/P AC	