










OPTIONAL CONSTRUCTION
SCALE 2:1



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE >PP< PER ISO 11469. (11)(10,1) CHARACTERS
AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER
THE LATEST REVISION OF ESD S1085201.
- RECOMMENDED HOLE SIZE $\varnothing .6.35$ IN 8 MAX THICK STOCK.
- THIS PART IS DESIGNED TO ACCEPT 6MM CPNVOLUTED CONDUIT.

15336095	02	AB	POLYPROPYLENE COMPOUND GRAY	1.599
12160859	03	AB	POLYPROPYLENE COMPOUND BLACK	1.599
PART NO	REV	N/P	MATERIAL SPECIFICATION AND COLOR	VOL CM ³

SYMBOL DEFINITION		MISSING NUMBERS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	5	
	LAST NO. USED	6	

CWS STATUS		REVISION HISTORY		AUTH		DR		APVD/APVD	
DATE	STG	REV	N/P	CHG	ZONE				
28JAN99	R	01	-	-		CLEARED REV COLUMN & ALL PARTS - REVISED	191393	AAS	JVM ET
22SEP00	R	02	-	-		REVISED DIM #252, ADDED DIM #325-326	201372	CJC	CJC ET
16MR01	R	03	-	-		REVISED TO DIMENSION # 323-324	207932	CJC	CJC ET
21JUN01	R	04	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES	211218	JLJ	JLJ ET
25SEP01	R	05	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES	214578	JMR	JMR ET
04OC02	R	06	-	-		12160859 - UPDATED PDM ATTRIBUTES	231462	BRB	BRB FR
11MR03	R	07	-	-		ALL PARTS - REVISED MATERIAL SPEC	238207	RH	RH ET
12JUN04	R	08	-	-		ALL PARTS - REVISED GRAPHICS	255789	JBD	JVM ET
25OC18	R	09	-	-		ALL PARTS - UPDATED DESIGN & ENGINEERING CONTROL AND ADDED NOTE	441293	LVD	JAA RJR

THE DESIGN AND ENGINEERING CONTROL OF
THIS COMPONENT HAS BEEN TRANSFERRED
TO APTIV/HELLERMANNTYTON

• APTIV •	
CONNECTION SYSTEMS	
COPYRIGHT 1997 APTIV. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DR	DATE
APV01 E. LUQUEÑO	26NOV97
APV02 L. R. MOYSEN M.	28NOV97
APV03 E. TRACEY	09DEC97
APV04	
APV05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 1094900	
DRAWING NAME	
TAXI MOUN CLIP CDT NAIL	
DRAWING NUMBER	
15336146	
SIZE A0	SCALE 5:1
FRAME NO 1 OF 1	SHEET NO 1 OF 1
STG R	REV 09

DIMENSIONAL RANGE (MM)		CHART ET	
FROM	TO	FROM	TO
> 0	> 20	> 70	> 100
> 20	> 30	> 100	> 150
> 30	> 40	> 150	> 200
> 40	> 50	> 200	> 250
> 50	> 60	> 250	> 300
> 60	> 70	> 300	> 400
TOLERANCE UNLESS OTHERWISE SPECIFIED		TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2		±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2	
ANGULAR TOLERANCE ±2°		ANGULAR TOLERANCE ±2°	

THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	USE MATH DATA