





DWG STATUS					ZONE	REVISION HISTORY				AUTH	DR	APV	APV2
DATE	STG	REV	N/P	CHG									
10MR03	R	01	-	-	ALL PARTS - REVISED MAT'L SPEC & 0891.1988 - UPDATED DWP ATTRIBUTES	238116	RVP	RVP	FR				
21MR03	R	02	-	-	ALL PARTS - REVISED MAT'L SPEC	238752	RVP	RVP	FR				
19OE03	R	03	-	-	0891.1988 - UPDATED DWP ATTRIBUTES	246172	BYT	BYT	ET				
14NO18	R	04	-	-	ALL PARTS - UPDATED DESIGN & ENGINEERING CONTROL AND ADDED NOTE	441471	JLL	JAA	RJR				




THE DESIGN AND ENGINEERING CONTROL OF
THIS COMPONENT HAS BEEN TRANSFERRED
TO APTIV/HELLERMANNTYTON




1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISION REQUIREMENTS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. MATERIAL RECYCLING CODE PER ISO 11469, 10.59(X)(0.003) CHARACTERS
AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
3. CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER
THE LATEST REVISION OF ESD S1085201.
4. THIS PART TO SNAP ONTO Ø.25 THREADED STUD.
5. THIS PART TO FIT .493 OR .406 I.D. CONVULGATED CONDUIT.

5		PROCESS SENSITIVE DIMENSION				
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED						
DIMENSIONAL RANGE (IN)		CHART		F		
FROM	0	>.750	>1.250	>2.750	>4.000	
TO	.750	1.250	2.750	4.000		
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.005		.010	.012	.016	.020	
ANGULAR TOLERANCE ±°						

A PART DRAWING THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING. PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING. CONTACT ACTIVELY SALES TO ASSURE AVAILABILITY OF PARTS. END TYPE	
PART DRAWING	
STITLE	
VOLUME 101 SEE CHART	DISTR CODE D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ANSI Y14.5-1994 AS FURNISHED BY THE SUPPLIER. DIMENSIONING AND TOLERDANCING ADAPTED FROM: ALL GEOMETRIC TOLERANCES (PER ISO 1101) AND SURFACE TEXTURES (PER ISO 4196) FROM AS UNLESS DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE BASED SEPARATELY. ALL DIMENSIONS ARE IN INCHES	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE USE MATH DATA  NX

• APTIV • CONNECTION SYSTEMS BARNEN, OH COPYRIGHT 1998 APTIV. ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.									
								DATE	
DR									
APV01		F. KOPCA				08AP98			
APV02		F. KOPCA				08AP98			
APV03		E. TRACEY				19AP99			
APV04									
APV05									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV (094900)									
MATERIAL									
SEE CHART									
DRAWING NAME									
TAXI MOUN CLIP CDT PUSH NUT									
DRAWING NUMBER									
15354735									
SIZE	SCALE	FRAME NO	SHEET NO	SHEET NO	STG	REV	REV	REV	REV
A0	5/16"	1	OF 1	1	OF 1	R	04		

A PART DRAWING THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING. PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING. CONTACT ACTIVELY SALES TO ASSURE AVAILABILITY OF PARTS. END TYPE	
PART DRAWING	
STITLE	
VOLUME 101 SEE CHART	DISTR CODE D
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ANSI Y14.5-1994 AS FURNISHED BY THE SUPPLIER. DIMENSIONING AND TOLERDANCING ADAPTED FROM: ALL GEOMETRIC TOLERANCES (PER ISO 1101) AND SURFACE TEXTURES (PER ISO 4196) FROM AS UNLESS DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE BASED SEPARATELY. ALL DIMENSIONS ARE IN INCHES	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE USE MATH DATA  NX