



SYMBOL DEFINITION			MISSING NUMBERS	
THE NUMBER INSIDE THE SYMBOL CORRESPONDS TO THE NUMBER ON THE INSPECTION REPORT FOR THIS DRAWING/PART NUMBER	TOTAL NO. OF SYMBOLS ON DRAWING	14		
	LAST NO. USED	16		

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
14MR03	R	01	-	-		CLEARED REV COL, ALL PARTS - ADDED NOTES (2 PLCS), REVISED MAT'L SPEC & 08917937 UPDATED PDM ATTRIBUTES	238428	RVP	RVP	FR
14N018	R	02	-	-		ALL - PARTS UPDATED DESIGN & ENGINEERING CONTROL AND ADDED NOTE	441471	JLL	JAA	RJR

THE DESIGN AND ENGINEERING CONTROL OF THIS COMPONENT HAS BEEN TRANSFERRED TO APTIV/HELLERMANNTYTON



- NOTES:
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSION) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - RECOMMENDED HOLE SIZE FOR CLIP .24 -.26 DIA HOLE IN .15 MAX THICK STOCK.
 - THIS PART TO FIT .493 I.D. CONVOLUTED CONDUIT.
 - DIMENSIONS MARKED WITH "*" MAY VARY FROM .185 -.165 AND .235 -.21 DUE TO BOW
 - DIMENSIONS MARKED WITH "▲" MAY VARY -.025 DUE TO BOW.
 - MATERIAL RECYCLING CODE PER ISO 11469. (0.06)X(0.004) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
 - CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER THE LATEST REVISION OF ESD S1085201.

DIMENSIONAL RANGE (IN)		CHART		H	
FROM	TO	0	1	2	3
0	.750	>.750	>1.250	>2.750	>4.000
.750	1.250	1.250	2.750	4.000	>4.000
1.250	2.750	2.750	4.000	>4.000	>4.000
2.750	4.000	4.000	>4.000	>4.000	>4.000
4.000	>4.000	>4.000	>4.000	>4.000	>4.000
TOLERANCE UNLESS OTHERWISE SPECIFIED					
ANGULAR TOLERANCE ±2°					

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	
PART DRAWING	
STYLE	
SEE CHART	
VOLUME (CM³)	DISTR CODE
SEE CHART	D
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE OM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY, REGARDLESS OF DATUM REFERENCE. ALL DIMENSIONS ARE IN INCHES	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	USE MATH DATA

• APTIV •	
CONNECTION SYSTEMS	
WARREN, OH	
COPYRIGHT 1997 APTIV. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DR	DATE
APVD1 E. MONCISVAIS	09DE97
APVD2 RAUL MOYSEN	09JA98
APVD3 E. TRACEY	09FE98
APVD4 E. TRACEY	29MR00
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001	
MATERIAL	
SEE CHART	
DRAWING NAME	
TAXI MOUN CLIP CDT ROSEBUD	
DRAWING NUMBER	
15336137	
SIZE	SCALE
A1	4:1
FRAME NO	SHEET NO
1 OF 1	1 OF 1
STG	REV
R	02
N/P	-

15336084	A5	-	POLYPROPYLENE COMPOUND GRAY	0.092
08917937	C7	-	POLYPROPYLENE COMPOUND BLACK	0.092
PART NO	REV	N/P	MATERIAL SPECIFICATION AND COLOR	VOL IN³