






SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	45
	LAST NO. USED	25

[illegible]

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. DIFFERENCE BETWEEN BOTH WINGS TO BE 0.3 MAX.
3. TERMINAL SYMMETRICAL ABOUT CENTERLINE EXCEPT AS SHOWN.

1. PLATING TYPE:
1. PLATE STOCK WITH 2.5-5.1 MICROMETERS ELECTROMATTE TIN
OVER 2.5-5.1 MICROMETERS ELECTRO COPPER.

PLATING TYPE INFORMATION SHOWN ABOVE IS FOR REFERENCE ONLY:
PLATING REQUIREMENTS ARE CONTAINED IN APPLICABLE MATERIAL
SPECIFICATIONS.

PFT-1404-29G	W	15583741	01	AC	UNSEALED	0.254X25.4	-	15518544	I	I	SN	SN	1-2	1.5-2	14	3.5	4.3	1.5 2.1	4	3.7	
PFT-1404-29	W	15518544	01	AC	UNSEALED	0.254X25.4	METL C14530 H0B HOT MECHANICAL WIPE TIN	TIN PLATED COPPER ALLOY	I	I	SN	SN	1-2	1.5-2	14	3.5	4.3	1.5 2.1	4	3.7	
PART NO	REV	PART NO	REV	N/P	SEALING	TERMINAL BODY BASE MAT'L THICKNESS	BASE MAT'L DESCRIPTION OR MADE FROM PART NUMBER	MATERIAL DESCRIPTION	CONTACT AREA PLATING TYPE	CRIMP AREA PLATING TYPE	CONTACT PLATING	CONTACT PLATING I.D.	SIZE (MM²)	DIA	ID	A±0.3	B±0.3	C	D	E±0.3	F±0.3
						BASE		DELPHI													
MVL																					

22		PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART	
FROM	0		
TO	12	> 12	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
	±0.1	±0.2	
ANGULAR TOLERANCE ±2°			

LINE DRAWN THROUGH A PART NUMBER
INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE
FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE
THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.

CONTACT DELPHI SALES TO ASSURE AVAILABILITY
OF PARTS.

DWG TYPE

PART DRAWING

STYLE

VOLUME (QTY)

DISTR CODE

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994
AND ASME Y14.100-1995, INCLUDING THE 2001 ADDENDUM
AND TOLERANCE ADDENDUM-2001. SEPARATE PATTERNS OF
DIMENSIONS MAY BE SHOWN SEPARATELY, IRRESPECTIVE OF
REFERENCES.

ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE

THIRD ANGLE PROJECTION	DO NOT SCALE	   
 	USE MATH DATA	

DELPHI

DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE

WARREN, OH

COPYRIGHT 1917 DELPHI CORPORATION AND/OR ITS AFFILIATES.
ALL RIGHTS RESERVED.

REVISED 2011

THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION
AND CONTAINS DELPHI CONFIDENTIAL INFORMATION.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION
OF THIS DOCUMENT OR ITS RELATED CO. WITH OTHERS,
WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

DATE	
DR	
DP#01 GERARDO DAVILA	22SE17
DP#02 JOSE O. GALLIGOS	22SE17
DP#03 VICTOR RETANA	22SE17
DP#04	
DP#05	

SUBSTANCES OF CONCERN AND RECYCLED
CONTENT PER DELPHI 10499001

MATERIAL
SHEET CHART

DRAWING NAME

TERM F MIXED UNKN

DRAWING NUMBER

15521606

SIZE	SCALE	FRAME	SHEET NO	STG	REV	NO
A0	1/4"	1 OF 1	1 OF 1	R	04	1