



SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL □ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	204
	LAST NO. USED	44


DWS STATUS					REVISION HISTORY				
DATE	STG	REV	N/P	CHG	ZONE				
10JA13	R	01	-	-		15521007 - RELEASED PART DRAWING	421071	EVV	EVV
10JA13	R	02	-	-		15521153 - RELEASED	421043	DCH	EVV
10JA13	R	03	-	-		15514892 - RELEASED	421058	DCH	EVV
10JA13	R	04	-	-		15514682 - RELEASED	421059	DCH	EVV
10JA13	R	05	-	-		15513495 - RELEASED	421060	DCH	EVV
26SE13	R	06	-	-		ALL PARTS - 48X Ø 0.8 ±0.05 TYP WAS 64X Ø 1 ±0.05 TYP, 16X Ø 3.12 ±0.1 TYP WAS 2X Ø 3.12 ±0.1 TYP, ADDED DIM 16X Ø 3.12 ±0.1 TYP, UPDATED CABLE O.D. NOTE AND REMOVED MATERIAL SAVERS	423928	ORA	JVM
28OC15	R	07	-	-		ALL PARTS - UPDATED PART AVAILABILITY	431282	AHY	DAT
22FE18	R	08	-	-		ALL PARTS - UPDATED "CABLE O.D." NOTE	439089	DAV	JVM




TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN





TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN





TYPE 105
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101

16X SEALING SURFACES
MUST BE FREE OF DEFECTS
AND PARTING LINE



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA. SEALING RIBS ARE IDENTICAL.
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EANP_4-3-CS-01-EN.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR - SEE CHART
- PARTS SHOWN ON THIS DRAWING USED IN ASSEMBLIES SHOWN ON TAXI - SEE CHART
- (1)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
- SEAL TO ACCEPT CABLE O.D. BETWEEN 1.2 AND 2.4 MM.

PART NO	REV	N/P	MATERIAL SPECIFICATION AND COLOR	TYPE	TAXI M CONN	TAXI ASM	A	B _{±0.15}	WAYS	VOLUME (CM³)
15513495	02	AB	SILICONE METHYL/VYNIL GREEN	105	15513469	15513480	13.48	15.4	6	0.768
15514682	02	AB	SILICONE METHYL/VYNIL GREEN	104	15514650	15514658	13.48	18.9	8	0.948
15514892	02	AB	SILICONE METHYL/VYNIL GREEN	103	15514806	15514813	13.48	22.4	10	1.126
15521153	02	AB	SILICONE METHYL/VYNIL GREEN	102	15521146	15521156	13.48	25.9	12	1.305
15521007	02	AB	SILICONE METHYL/VYNIL GREEN	101	15521019	15521026	13.48	32.9	16	1.664

19 PROCESS SENSITIVE DIMENSION										REFERENCE										DRAWING NAME									
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED																				TAXI SEAL CBL/CONN									
DIMENSIONAL RANGE (MM)										THIRD ANGLE PROJECTION										DRAWING NUMBER									
FROM TO 0 20 30 40 50 60 70 80 90 100 120 150 200 250 300 400										DO NOT SCALE										15521008									
TOLERANCE UNLESS OTHERWISE SPECIFIED										USE MATH DATA										SIZE A SCALE 5:1 FRAME NO 1 OF 1 SHEET NO 1 OF 1 STB REV R8 N/P -									
±0.151 ±0.121 ±0.1 ±0.075 ±0.051 ±0.038 ±0.025 ±0.012										NX																			