KEY PRODUCT CHARACTERISTICS			
SAFETY/COMPLIANCE	FIT/FUNCTION	TOTAL ON DRAWING	1
S/C CHECKPOINTS	F/F CHECKPOINTS	LAST NO. USED	1

NO	TYPE	DESCRIPTION	RATIONALE	PTS	ZONE
1	FF	WIDTH CONNECTOR			F12

SYMBOL DEFINITION

A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL (□) DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.

TOTAL NO OF INSPECTIONS REQUIRED	6
LAST NO. USED	6

MISSING SYMBOLS

NO MISSING SYMBOL NUMBER

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR APVD	APVD DATE
DATE	STS	REL	N/P	CHG					
03NO21	R	01	-	-	-	ALL PARTS - RELEASED DISTRIBUTABLE PART DRAWING	955675	AMV	JAA 03NO21
16APR24	R	02	-	-	-	3581B342 - RELEASED	563575	GLO	CSO 03MAY24
26FEB26	R	03	-	-	-	3511306 - OBSOLETE; 3511308-12 - OBSOLETE; 3511314-23 - OBSOLETE; 3520080 & 81 - OBSOLETE	572302	AOC	JAA 26FEB26



CODE B
SAME AS CODE A
EXCEPT AS SHOWN



CODE D
SAME AS CODE A
EXCEPT AS SHOWN



CODE C
SAME AS CODE A
EXCEPT AS SHOWN





SECTION AAB-AAB







CODE A



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

   DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EMP-4.1-CS_01-EN.

3. WIRING FABRICATORS MUST PURCHASE FROM SOURCES SHOWN.

4. ALL THE SEALED CONNECTOR APPLICATIONS MUST BE USED WITH CHRYSLER WIRE SPEC, MS-B288, MS-9502 OR ISO 6722 EQUIVALENTS THIN WALL X-LINK ONLY.
   A- ASSEMBLIES WITH MVL P/N'S 54200239 OR 54200240 END SEALS MUST BE USED WITH 20 TO 14AWG OR ISO EQUIVALENTS WIRES WITH INSULATION Ø1.70 TO Ø2.8 O.D.

   B- ASSEMBLIES WITH MVL P/N'S 54200241 OR F480510 END SEALS MUST BE USED WITH 14 TO 10AWG OR ISO EQUIVALENTS WIRES WITH INSULATION Ø2.50 TO Ø4.09 O.D.

5. MVL P/N'S 5420023B RING SEAL, 54200240 AND F480510 END SEALS BAKED AT 450° F FOR 5 HOURS TO DRIVE OFF VOLITILES.

6. DIRECT CONNECT INTERFACE PER MVL 036002 (CHRYSLER 47070271).

7. TEST METHOD PER SAE/USCAR-2 REV.5, CONNECTOR ENGAGE & DISENGAGE WITH LATCH DEPRESSED FORCE NOT TO EXCEED 75N FOR THIS SYSTEM.

   CPA SEATING FORCES - 40N MAX.

   WEDGE SEATING FORCES - 100N MAX.

   X-MAS TREE CLIP INSERTION FORCES - 75N MAX.

8. MVL SUPPLIER CODE 52772, MOLD & CAVITY I.D. SIGNIFIES TOOL OWNERSHIP FOR REFERENCE.

9. ANNUAL QUALITY REQUIREMENTS:
   IT IS PERMISSIBLE TO PERFORM CONTINUOUS CONFORMANCE PER MVL SPECIFICATION 4424-001 INSTEAD OF ANNUAL LAYOUT & ANNUAL PV REQUIREMENTS OF QS-9000 SECTION 2 & SAE/USCAR-2.

10. SERVICE TOOLING GUIDE INFORMATION PER APEX TRAINING MANUAL

    ** MVL P/N 54200259 NOT PRODUCED USE MVL P/N 55200200

11. MVL P/N WITH SUFFIX "N" DESIGNATES ASSEMBLIES WITHOUT CPA.

12. MUST BE USED WITH FLUOROSILICONE END SEAL MVL P/N 54202065 DPN 13517371, RETAINER P/N 54202024 DPN 15537420 AND PROPER GAGE TEFLON WIRES FOR FLEX FUEL APPLICATIONS. ASSEMBLE TERMINALS THROUGH RETAINER AND END SEAL PRIOR TO ASSEMBLING INTO TERMINAL CAVITY.

13. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.

14. CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER THE LATEST REVISION OF ESD S1085201.

15. ASM CONN PN 3581B342 WAS ANALYZED FOR CREEPAGE & CLEARANCE FOR 48 VOLTS

PART NO	REV	N/P	CODE	PART NO.	PCL	HOUSING		PLR		SEAL CONN		CBL SEAL		RETAINER		CPA		REPLACED BY	TEMP CLASS
APTIV				MVL		MVL	APTIV	MVL	APTIV	MVL	APTIV	MVL	APTIV	MVL	APTIV	MVL	APTIV		
13511423	01	AC	D	F970510	A	54200258	15537449	54200225	15537306	5420023B	15537426	F480510	N/A	54200234	15537420	54200003	15537297		4
13511422	01	AC	C	F870510	A	54200257	15537447	54200225	15537306	5420023B	15537426	F480510	N/A	54200234	15537420	54200003	15537297		4
13511421	01	AC	B	F770510	A	54200256	15537445	54200225	15537306	5420023B	15537426	F480510	N/A	54200234	15537420	54200003	15537297		4
13511420	01	AC	A	F670510	A	55200201	15537438	54200225	15537306	5420023B	15537426	F480510	N/A	54200234	15537420	54200003	15537297		4
13585482	01	AG	D	54200262	T	54200258	15537449	54200281	15537462	5420023B	15537426	54200240	15537437	54200271	15537460	5420000B	15537298		4
13585481	01	AG	C	54200261	T	54200257	15537447	54200281	15537462	5420023B	15537426	54200240	15537437	54200271	15537460	5420000B	15537298		4
13585480	01	AG	B	54200260	T	54200256	15537445	54200281	15537462	5420023B	15537426	54200240	15537437	54200271	15537460	5420000B	15537298		4
13511419	01	AD	A	55200200N	S	55200201	15537438	54200281	15537462	5420023B	15537426	54200240	15537437	54200271	15537460				4
13596027	01	AE	A	55200200	S	55200201	15537438	54200281	15537462	5420023B	15537426	54200240	15537437	54200271	15537460	54200008	15537298		4
13511418	01	AC	A	••54200259	S	54200255	N/A	54200225	15537306	5420023B	15537426	54200240	15537437	54200234	15537420	54200003	15537297	13596027	4
13511417	01	AC	A	54200213N	S	54200227	15537310	54200225	15537306	54200237	15537424	54200241	15537441	54200234	15537420	-	-		3
13511416	01	AC	A	54200212N	S	54200231	15537319	54200225	15537306	5420023B	15537426	54200240	15537437	54200234	15537420	-	-		3
13511415	01	AC	D	54200209N	S	54200230	15537317	54200225	15537306	54200237	15537424	54200239	15537436	54200234	15537420	-	-		3
13511414	01	AC	C	54200208N	S	54200229	15537315	54200225	15537306	54200237	15537424	54200239	15537436	54200234	15537420	-	-		3
13511313	01	AB	B	54200207N	S	54200228	15537313	54200225	15537306	54200237	15537424	54200239	15537436	54200234	15537420	-	-		3
13802955	01	AD	A	54200214N	S	54200227	15537310	54200225	15537306	54200237	15537424	54200239	15537436	54200234	15537420	-	-		3
13500084	01	AB	A	54200213	S	54200227	15537310	54200225	15537306	54200237	15537424	54200241	15537441	54200234	15537420	54200003	15537297		3
13581967	01	AF	A	54200212	S	54200231	15537319	54200225	15537306	5420023B	15537426	54200240	15537437	54200234	15537420	54200003	15537297		3
13768919	01	AC	D	54200209	S	54200230	15537317	54200225	15537306	54200237	15537424	54200239	15537436	54200234	15537420	54200003	15537297		3
13848326	01	AC	C	54200208	S	54200229	15537315	54200225	15537306	54200237	15537424	54200239	15537436	54200234	15537420	54200003	15537297		3
15180781	01	AH	B	54200207	S	54200228	15537313	54200225	15537306	54200237	15537424	54200239	15537436	54200234	15537420	54200003	15537297		3
13511412	01	AC	A	54200263	U	54200227	15537310	54200225	15537306	54200264	13517371	-	-	-	-	-	-		3
3581B342	01	-	A	-	-	3581B338	15537438	54200225	15537306	54200237	15537424	54200239	15537436	54200234	15537420	54200003	15537297		3
10757672	01	AB	A	54200206	S	54200227	15537310	54200225	15537306	54200237	15537424	54200239	15537436	54200234	15537420	54200003	15537297		3
13506481	01	AC	D	54200203	S	54200230	15537317	54200225	15537306	-	-	-	-	-	-	54200003	15537297		3
13506480	01	AC	C	54200202	S	54200229	15537315	54200225	15537306	-	-	-	-	-	-	54200003	15537297		3
13581772	01	AG	B	54200201	S	54200228	15537313	54200225	15537306	-	-	-	-	-	-	54200003	15537297		3
13869306	01	AC	A	54200200	S	54200227	15537310	54200225	15537306	-	-	-	-	-	-	54200003	15537297		3
13511411	01	AC	A	54200251	S	54200231	15537319	54200225	15537306	-	-	-	-	-	-	54200003	15537297		3
13511410	01	AC	D	54200230N	S	54200230	15537317	54200225	15537306	-	-	-	-	-	-	-	-		3
13511409	01	AC	C	54200229N	S	54200229	15537315	54200225	15537306	-	-	-	-	-	-	-	-		3
13511408	01	AC	B	54200201N	S	54200228	15537313	54200225	15537306	-	-	-	-	-	-	-	-		3
13511307	01	AB	A	54200200N	S	54200227	15537310	54200225	15537306	-	-	-	-	-	-	-	-		3
13511426	01	AC	A	54200253N	S	54200231	15537319	54200225	15537306	-	-	-	-	-	-	-	-		3

SEE NOTE #5

DRAWING NUMBER: 15443179							
SIZE	SCALE	FRAME NO	SHEET NO	TOTS	REV	NOT
A1x3	4:1	2 OF 2	1 OF 1	R	03	-

(N/A) PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN ( ) INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE UNLESS OTHERWISE SPECIFIED	

DIMENSIONAL RANGE (MM)								
FROM	0.5	6	30	120	315	1000	2000	3150
TO	6	30	120	315	1000	2000	3150	4000
TOLERANCE UNLESS OTHERWISE SPECIFIED	±0.15	±0.2	±0.3	±0.5	±1.0	±2.0	±3.0	±4.0

ANGULAR TOLERANCE ±0.5°

THIRD ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

NX

MATERIAL	TAXI CONN 2 F APEX 2.8 SLD
FINISH	
COLOR	
PART NAME	PART DRAWING
STYLE	
VOLUME (CM³)	
SYSTEM USE	D

UNLESS OTHERWISE SPECIFIED
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994
ALL DIMENSIONS ARE IN MILLIMETERS
TOLERANCING PRINCIPLE: PER ASME Y14.5M-1994
GEOMETRIC TOLERANCING: SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES

ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE:

APVD1	MA. ANTONIETA HDZ
APVD2	J.G. ALVARADO
APVD3	JESUS ACUNA
APVD4	
APVD5	

DR	0JN021
APVD1	0JN021
APVD2	04NO21
APVD3	
APVD4	
APVD5	

NEXT ASSY: SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV STANDARD

NEXT ASSY	SEE CHART
DRAWING NAME	TAXI CONN 2 F APEX 2.8 SLD
DRAWING NUMBER	15443179

SIZE	SCALE	FRAME NO	SHEET NO	TOTS	REV	NOT
A1x3	1:1	OF 2	1 OF 1	R	03	-

COPYRIGHT 2021 APTIV, ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. NEITHER THIS DRAWING NOR THE INFORMATION IN IT MAY BE USED FOR MANUFACTURE OR ITS RELATED ITEM WITH DATA, NOR WILL IT BE COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

CONNECTION SYSTEMS	
WARREN, OH	

Plotted: 26FEB26 11:44:18 AM
Saved: 26FEB26 11:44:18 AM