





SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL □ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	6	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	6		


CWS STATUS				REVISION HISTORY				AUTH		DR		APVD	
DATE	STG	REV	N/P	CHG	ZONE								
04MY04	R	01	-	-		CLEARED REV COL & REDRAWN TO PD: 12010718 - REVISED PER NIN EWO BOLTS; 12010718, 12041416 & 12010149 - UPDATED MAT'L SPEC, ADDED DIM A		254568	JPB	FRB	MR		
03MR05	R	02	-	-		ALL PARTS - ADDED ALTERNATE MAT'L SPEC COLUMN: 12010718 - MAT'L SPEC M3471007 WAS M3467007; 12020455, 12041416 REVISED NOTES 5 & 6; 12010155, 12010227, 12010492 & 12020455 - UPDATED MAT'L SPEC		265443	JBD	JVM	MR		
04OC09	R	03	-	-		ALL PARTS - ADDED VOLUME COLUMN ON CHART		409019	MAL	ECB	DGL		
02FE10	R	04	-	-		12020455 & 12041416 - OBSOLETE		409863	JVM	JVM	MPR		




TYPE 606




TYPE 601
SAME AS TYPE 606
EXCEPT AS SHOWN



TYPE 602
SAME AS TYPE 606
EXCEPT AS SHOWN




TYPE 603
SAME AS TYPE 606
EXCEPT AS SHOWN




SEALING RIBS MUST BE FREE OF SINKS, VOIDS, KNIT LINES AND FLASH.

FLASH AT INJECTION AREAS NOT TO EXCEED 0.4 HIGH BY 0.8 THICK



TYPE 604
SAME AS TYPE 606
EXCEPT AS SHOWN



TYPE 605
SAME AS TYPE 606
EXCEPT AS SHOWN

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. PARTS ARE TO BE PACKAGED IN SEALED PLASTIC BAGS. GROSS WEIGHT INCLUDING CARTON IS NOT TO EXCEED 34 POUNDS.
3. "▲" DENOTES DIMENSIONS THAT ARE CONTROLLED FOR AUTOMATIC PROCESSING.
4. SEALING RIBS ARE IDENTICAL.
5. P/N 12020455 MATES TO (DELCO) BX-45528.
6. P/N 12041416 MATES TO (ALLIED CHEMICAL) DIESEL GLOW PLUG CONTROLLER.
7. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.

PART	NO	REV	N/P	STATUS	TYPE	MATERIAL SPEC	ø A	C▲	D▲	P▲	REPLACED BY	TYPICAL MATTING CONNECTOR (REF)	VOLUME (CM³)
12041416	A4	-	OBSOLETE	605		SILICONE METHYL/VINYL ORANGE	5.5	41.8±0.15	11	6	-	SEE NOTE #6	1.348
12020455	B3	-	OBSOLETE	605		SILICONE METHYL/VINYL GREEN	5.85	41.8±0.15	11	6	-	SEE NOTE #5	1.348
12010718	07	AA	-	603		SILICONE METHYL/VINYL GREEN	5.85	26.4 ±0.25/-0.4	11	6	-	12010716	0.805
12010492	C2	-	-	604		SILICONE METHYL/VINYL GREEN	5.85	34.1 ±0.15/-0.61	11	6	-	12010491	1.077
12010227	F2	-	-	606		SILICONE METHYL/VINYL GREEN	5.85	49.5 ±0.15/-0.55	11	6	-	12010226	1.619
12010155	F2	-	-	602		SILICONE METHYL/VINYL GREEN	5.85	18.7 ±0.15/-0.42	11 ±0.15/-0.3	6	-	12010153	0.534
12010149	E3	-	-	601		SILICONE METHYL/VINYL GREEN	5.85	11	11	8.05	-	12010147	0.310

2 PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	
FROM	0 > 20 > 30 > 70 > 100 > 100
TO	20 30 70 100 100
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.15 ±0.2 ±0.3 ±0.4 ±0.5	
ANGULAR TOLERANCE ±2°	

THIRD ANGLE PROJECTION		DO NOT SCALE	
USE MATH DATA		USE MATH DATA	

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH	
DATE	
APVD1 PEDRO YABUR	02 JUN94
APVD2 D. BRANTINGHAM	06 JUN94
APVD3 K.D. MURPHY	27 JUN94
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 13049001	
MATERIAL SEE CHART	
DRAWING NAME	
TAXI SEAL CONN	
DRAWING NUMBER	
12077524	
SIZE A0	SCALE 5:1
FRAME NO 1	SHEET NO 1 OF 1
STG R	REV 04