







[illegible]

NOTES:

1. RECOMMENDED HOLE SIZE FOR CLIP: 6.6/6.1 DIA. HOLE IN 3.80 MAX. THICK STOCK
2. THIS PART DESIGNED TO ACCEPT 10 TO 13 MM CONVOLUTED CONDUIT.
3. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSION)
FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR
TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
4. DIMENSIONS MARKED "REF" ARE FOR REFERENCE ONLY
AND NO TOLERANCE LIMITS ARE ESTABLISHED.
5. MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1) RAISED
CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
6. (2.3)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON
ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

DRAWING TYPE PID		OTHER DRAWINGS AVAILABLE DETAIL	
		METRIC DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED	
		TOLERANCE UNLESS OTHERWISE SPECIFIED DECIMAL: ANGULAR ± 2	
THIRD ANGLE PROJECTION		ONE PLACE ± 0.3 TWO PLACE ± 0.15	
CODE NO	QC	DES	
6900	-C-4004		
DWG DATE	26AUB8	DR T.E.MC KEE JR.305EB	
SCALE	4:1	CK F. HESTON 305EB	
REFERENCE NO		APPRJ.JAY GRABIEC 030CB	
08905799 & 12084887		VOL CM ³ 2.155	
MATERIAL SPEC			
M2097001 PP IM BLK			
NAME			
CLIP CNVLT CDT 10/13MM			
PART NUMBER			SIZE
1209 2091			A1