





CUSTOMER DRAWING



1. 02506FLC14FA-B ASSY




ISO VIEW







SECTION A-A



2. F/H 02506FLC14FA-GN



ISO VIEW



- NOTES -

- 1. BEFORE USING, CHECK THE HARFUL CRACK, BURR, ETC.
- 2. GENERAL TOLERANCE - SEE BELOW.
- 3. MARKING & CAV No. BY AS GENERAL RULE OF KUM.
- 4. ASSY PARTS

- 1) FRONT HOLDER: GL302-14030 / 33111635
- 2) CONNECTOR SEAL: ES026-10120 / 35338446
- 3) TERMINAL

SERIES	APPLICATION WIRE(SQ)	KUM PART NAME	KUM P/No.	APTIV P/No.
025	AESSX(F) 0.3~0.5sq	TML TWP-F-S	TP105-00100	15517490
060	AEX(F), AESSX(F) 0.75~1.25sq	TML AWP-F-M	TP135-00200	15533096
	AEX(F), AESSX(F) 0.3~0.5sq	TML AWP-F-S	TP135-00100	15533095

4) WIRE SEAL

SERIES	APPLICATION WIRE DIAMETER	KUM PART NAME	KUM P/No.	APTIV P/No.
025	Φ0.9 ~ Φ1.1	W/S TWP-0.9S(MB)	EU020-01140	35187200
	Φ1.4 ~ Φ1.5	W/S TWP-1.4S(BR)	EU020-01050	15517491
	Φ1.6 ~ Φ1.7	W/S TWP-1.6S(GN)	EU020-00030	15523552
	-	W/S TWP-V(R)	EU020-00060	15517565
060	Φ0.9 ~ Φ1.3	W/S AWP-0.9S(MB)	EB010-01140	35235729
	Φ1.4 ~ Φ1.8	W/S AWP-1.4S(BR)	EB010-01050	15533092
	Φ1.9 ~ Φ2.2	W/S AWP-1.9S(GN)	EB010-01030	15533091
	Φ2.3 ~ Φ2.6	W/S AWP-2.3S(GY)	EB010-01120	35283152
	Φ2.7 ~ Φ2.9	W/S AWP-2.7S(OR)	EB010-01100	35283153
	-	W/S AWP-V(R)	EB010-01060	33370412

5. ASSY P/NO.

KUM PART NAME	KUM P/No.	APTIV P/No.	①	②	③
02506FLC14FA-B ASSY	GL301-14021	15533094	●	●	●

6. THIS IS A WATERPROOF CONNECTOR.

7. APTIV Drawing No : 15533094

GENERAL TOLERANCE						
	10MAX	50MAX	100MAX	150MAX	200MAX	200VR
A	±0.2	±0.3	±0.5	±0.8	±1.0	±1.4

③	F/H 02506FLC14FA-GN	GL302-14030	33111635	GREEN	PBT
②	C/S XWP10PA-GY	ES026-10120	35338446	GRAY	SI-RUBBER
①	02506FLC14FA-B	GL301-14020	35298588	BLACK	PBT
NO.	KUM PART NAME	KUM P/No.	APTIV P/No.	COLOR	MATERIAL
THIRD ANGLE PROJECTION	A	-	MDK	PJW	JSJ
	TOLERANCE	SCALE	DESIGN	DRAWN	CHECKED

MDG	19.JUN.25Y	-	△	RELEASED	CSH
APV	DATE	NOTE No.	SYM	ALTERATION	DWN
DRAWING NAME					02506FLC14FA-B ASSY
DRAWING No.					GL301-14021-C01
• APTIV •					