






THE DESIGN AND ENGINEERING CONTROL OF
THIS COMPONENT HAS BEEN TRANSFERRED
TO APTIV/HELLERMANNTYTON



1. MATING COMPONENTS:
CONNECTOR 12110727 & 12110721 OR EQUIVALENT
2. DIMENSIONS MARKED "REF" ARE FOR REFERENCE ONLY, AND NO TOLERANCES LIMITS ARE ESTABLISHED.
3. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE TOOL PATH DATA.) FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
4. THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
5. CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER
THE LATEST REVISION OF ESD S1085201.

TOLERANCE OTHERWISE DECIMAL:	UNLESS SPECIFIED ANGULAR ± 2
ONE PLACE	± 0.3
TWO PLACE	± 0.15

Isar: J2K9z
 Part: 210725-CUS01-50103AD
 Date: 27-Nov-18 Time: 10:27:22