






- | | | | |
|--|------|-----------------------------|--|
| 2 | | PROCESS SENSITIVE DIMENSION | |
| DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED | | | |
| DIMENSIONAL RANGE (MM) | | CHART D | |
| FROM | 0 | | |
| TO | 12 | >12 | |
| TOLERANCE UNLESS OTHERWISE SPECIFIED | | | |
| | ±0.1 | ±0.2 | |
| ANGULAR TOLERANCE ±2° | | | |

•APTIV•

CONNECTION SYSTEMS

WARREN, OH

COPYRIGHT 1986 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV'S
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
UTILIZATION OF THIS DOCUMENT OR ITS RELATED DATA WITH DATA, AS WELL
AS COMMUNICATION OF AND CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

DR	DATE
AP101 J. A. VILLEGAS	16NOV16
AP102 J. A. VILLEGAS	16NOV16
AP103 CRYSTAL KROMPEGAL	16NOV16
AP104	
AP105	

SUBSTANCE OF CONCERN AND RECYCLED
CONTENT PER APTIV 10949001

MATERIAL SEE CHART

DRAWING NAME:

TAXI TERM M FAKRA PLUG AU

DRAWING NUMBER

35014615

SIZE	SCALE	FRAME	NO	SHEET	NO	STO	REV	NO
A0	1X=1	1	1	1	1	1	0	1

35194027	03	-	102	35340124	02	-	0.178 X 16.51	METAL COPPER ALLOY	0.18 - 0.25 MM ²	0.48 - 0.56 MM	1.24	1.5	2.5	35013992
35176709	03	-	101	35340127	02	-	0.178 X 16.51	METAL COPPER ALLOY	0.18 - 0.25 MM ²	0.48 - 0.56 MM	1.24	1.5	2.5	35013992
35061156	03	-	101	35340126	02	-	0.178 X 16.51	METAL COPPER ALLOY	0.75 - 0.8 MM ²	0.98 - 1.01 MM	2.22	2.4	2.5	35013992
35064154	03	-	102	35340123	02	-	0.178 X 16.51	METAL COPPER ALLOY	0.1 - 0.18 MM ²	0.36 - 0.48 MM	1.24	1.34	2.5	35013992
33229390	04	-	101	35340128	02	-	0.178 X 16.51	METAL COPPER ALLOY	0.1 - 0.18 MM ²	0.36 - 0.48 MM	1.24	1.3	2.5	35013992
33229389	04	-	101	35340125	02	-	0.178 X 16.51	METAL COPPER ALLOY	0.35 - 0.5 MM ²	0.67 - 0.8 MM	2	2.1	2.5	35013992
PART NO	REV	N/P	TYPE	PART NO	REV	N/P								
PLATED				PRE-PLATED (SEE NOTE #6)		MAT'L SIZE		MAT'L SPEC	CORE AREA (MM ²)	NOM. CORE O.D. (MM)	B ₁ ±0.15	(H ₁)	L ₁	USED ON ASSEMBLY TAX I