






2. 1.43 MAX ALLOWABLE SHEET METAL THICKNESS.



14. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER NAP 4.10-18.

DWG STATUS					ZONE	REVISION HISTORY		AUTH	DR	APPROVAL	
DATE	STS	REV	N/P	CHG						1	2
10F0C3	R	C2	-	-	ADDED NOTES (2 PLCS)		236963	RCH	RCH	JH	
07MR03	R	C3	-	-	ADDED SYMBOLS (13 PLCS) & NOTES (3 PLCS)		238006	RCH	RCH	JH	
05OC04	R	03	AD	-	REVISED TOLERANCES - 2PLCS; REVISED NOTE 9		259886	ADK	ADK	6D	
15AP08	R	04	-	-	NUT 13705809 WAS NUT 6M 21006316		404394	JAV	JAV	JAV	
22SE08	R	04	AA	-	ADDED LABEL "SEE DETAIL D" ON SECTION A-14 AND TOLERANCE DIMENSION WAS 17		406153	AC9	FKV	SLS	

ALL DIMENSIONS ARE IN MILLIMETERS(N/A) PROCESS SENSITIVE DIMENSION																																							
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED REFERENCE																																							
DIMENSIONS (UNLESS RANGE IS SHOWN) <table><tr><th>FROM</th><th>> 0</th><th>> 0</th><th>> 0</th><th>> 0</th></tr><tr><td>TO</td><td>20</td><td>30</td><td>40</td><td>50</td></tr></table>					FROM	> 0	> 0	> 0	> 0	TO	20	30	40	50	CHART B1 <table><tr><th>TO</th><th>20</th><th>30</th><th>40</th><th>50</th><th>60</th><th>70</th><th>80</th><th>90</th><th>100</th></tr><tr><th>FROM</th><td>10</td><td>15</td><td>20</td><td>25</td><td>30</td><td>35</td><td>40</td><td>45</td><td>50</td></tr></table>					TO	20	30	40	50	60	70	80	90	100	FROM	10	15	20	25	30	35	40	45	50
FROM	> 0	> 0	> 0	> 0																																			
TO	20	30	40	50																																			
TO	20	30	40	50	60	70	80	90	100																														
FROM	10	15	20	25	30	35	40	45	50																														
TOLERANCE UNLESS OTHERWISE SPECIFIED <table><tr><th>±0.15</th><th>±0.2</th><th>±0.3</th><th>±0.4</th><th>±0.5</th><th>±0.6</th><th>±0.8</th><th>±1</th><th>±1.2</th></tr><tr><td>±0.15</td><td>±0.2</td><td>±0.3</td><td>±0.4</td><td>±0.5</td><td>±0.6</td><td>±0.8</td><td>±1</td><td>±1.2</td></tr></table>										±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2												
±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2																															
±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2																															
ANGULAR TOLERANCES THIRD ANGLE PROJECTION DO NOT SCALE USE MATH DATA																																							

											
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH											
DR					DATE						
APV01 TOM NADASKY					30 JA92						
APV02 J.P. LITTLEFIELD					27MR92						
APV03 J.P. LITTLEFIELD					27MR92						
APV04											
APV05											
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949901											
MATERIALS DRAWING											
DRAWING NAME											
ASM COV MODULE											
DRAWING NUMBER											
12129121											
SIZE A0		SCALE 1:1		FRAME NO 1 OF 1		SHEET NO 1 OF 1		STS R 04		REV N/A	