


SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	NO MISSING SYMBOL NUMBER	
	LAST NO. USED		
	11		
	11		

DWG STATUS				REVISION HISTORY				AUTH		DR		APVD	
DATE	STG	REV	N/P	CHG	ZONE								
28MY99	R	01	-	-		ALL PARTS - REDRAWN TO PD		990009	PHC	MVA		ET	
12MR01	R	02	-	-		UPDATED PDM ATTRIBUTES		207450	JLJ	JLJ		ET	
20SE01	R	03	-	-		ALL PARTS - ADDED OPTIONAL CONSTRUCTION: ADDED NOTE		214860	TSH	TSH		ET	
03OC02	R	04	-	-		12176839 - UPDATED PDM ATTRIBUTES		231443	HAM	HAM		FR	
04FE03	R	05	-	-		ALL PARTS - REVISED MAT'L SPEC		236326	RH	RH		ET	
18AU05	R	06	-	-		ALL PARTS - ADDED DRAWING NAME		271160	JTZ	FRG		TP	
09.N06	R	07	-	-		REVISED NOTE 5		281525	MM	MM		ET	
09N018	R	08	-	-		ALL PARTS - UPDATED DESIGN & ENGINEERING CONTROL AND ADDED NOTE		441375	LVD	JAA	RJR		

THE DESIGN AND ENGINEERING CONTROL OF THIS COMPONENT HAS BEEN TRANSFERRED TO APTIV/HELLERMANNTYTON



SCALE 2:1

SEE NOTE #4

OPTIONAL CONSTRUCTION

SCALE 2:1

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- RECOMMENDED HOLE SIZE FOR CLIP: $\varnothing$ 6.675 $\pm$ 0.325 HOLE IN 12.5 MAX THICK STOCK.
- THIS PART TO ACCEPT 16MM CONDUIT.
- NO PROTRUDING GATES, SHARP EDGES OR PROTRUSIONS ALLOWED IN THIS AREA.
- MATERIAL RECYCLING CODE PER ISO 11469. (0.11X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
- CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER THE LATEST REVISION OF ESD S1085201.

15336097	A8	-	POLYPROPYLENE COMPOUND GRAY	2.017
12176839	B11	-	POLYPROPYLENE COMPOUND BLACK	2.017
PART NO	REV	N/P	MATERIAL SPECIFICATION AND COLOR	VOLUME

		1		PROCESS SENSITIVE DIMENSION	
		DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)				CHART E	
FROM	TO	> 0	> 30	> 100	> 200
0	20	0.15	0.2	0.15	0.2
		TOLERANCE UNLESS OTHERWISE SPECIFIED			
		±0.1	±0.4	±0.5	±0.8
		ANGULAR TOLERANCE ±2°			