









MISSING SYMBOLS	DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD	APVD
	DATE	STG	REV	N/P	CHK						
NO MISSING SYMBOL NUMBER	04NO15	R	01	-	-		ALL PARTS - RELEASED PART DRAWING	430761	KA	KA	SSS
	17MR16	R	02	-	-		REMOVED THIRD INTERNAL CONDUIT RIB	432094	RAK	RAK	SSS
	30JUN16	R	03	-	-		REVISED INTERCHANGEABLE TOL NOTE & TOLS ON DIM (5 PLCS) AND SEPARATED FEATURE CONTROL FRAME ON DIMS #6 & #27	432604	SM	SM	SSS
	18AUG16	R	04	-	-		REVISED TOL ON DIM #14	433919	SM	SM	SSS
	06SEP16	R	05	-	-		REVISED DIM (4 PLCS)	433973	SM	SM	SSS
	06OCT16	R	06	-	-		ADDED NOTES	434475	KA	KA	DDJ
	21NOV16	R	07	-	-		REVISED ACCEPTANCE CRITERIA DEVIATIONS NOTE	434971	SM	SM	DDJ
	27APR17	R	08	-	-		ALL PARTS - ADDED BASIC DIM 10.7, DIM #17 WAS 4.8 +0.13/-0 & DIM #26 WAS 2X Ø7.2 +0.1 TYP AND REVISED DIM #26 FEATURE CONTROL FRAME	436472	NKS	RRR	DDJ
	05JUN17	R	09	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES	436882	NKS	NKS	DDJ
	27JUL17	R	10	-	-		ALL PARTS - DIM #21 WAS 2X 4.8 +0.25/-0 AND ADDED DIM 2X [5]	437323	NKS	NKS	DDJ
	21NOV17	R	11	-	-		ALL PARTS - REMOVED DIM #34 & 35, CORRECTED DIM #6 & 27 AND UPDATED PART AVAILABILITY	438294	JSK	JSK	DDJ
	05FEB18	R	12	-	-		ALL PARTS - ADDED DIM #34 & BASIC DIM (6 PLCS) DIM #14 WAS 2X 16.3 +0.1/-0.18, BASIC DIM 2X Ø1.1 TYP WAS BASIC DIM 5Ø1.1, MOVED BASIC DIM 10.7 TO SEC VIEW "A-A", REVISED FEATURE CONTROL FRAME ON DIM #6 & #27 AND REMOVED BASIC DIM 2X 16.6 TYP	438947	JSK	JSK	DDJ



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA
2. MATERIAL RECYCLING CODE PER ISO 11469. (1.5)X(11) CHARACTERS PA 66 LOCATED ON ANY EXTERIOR SURFACE
3. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-C5-01
4. REFERENCE MATING COMPONENTS OR EQUIVALENT:


TAXI: 33288232, 33299377 & 33299375 2, 3 & 4-WAY DRESS COVERS
5. 90° ELBOW FOR 2, 3 & 4-WAY DRESS COVERS
6. (1.5)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY
7. INTERCHANGEABLE TOOL FOR 6MM, 9MM AND NO CONDUIT (CDT) OPTIONS
8. EJECTOR PIN NOTES:
ENGAGEMENT SURFACE: FLUSH TO 0.15 MAX RECESSED
TOP SURFACE: FLUSH TO 0.05 MAX RECESSED
ALL OTHERS: 0.10 MAX RAISED TO 0.25 MAX RECESSED
9. ACCEPTANCE CRITERIA DEVIATIONS:

35N MIN FOR BACKSHELL LOCKED RETENTION AT WIRE EXIT POINT

50N MIN FOR CONDUIT TO BACKSHELL RETENTION AND CONNECTOR TO BACKSHELL RETENTION UNDER SIDE LOAD

33292356	03	AG	NO CONDUIT	NO CODE	3.086	
33275463	04	AG	9 (M1889002/M1889012)	9	3.156	
33292355	04	AG	6 (M1889001/M1889011)	6	3.201	
PART	NO	REV	N/P	CONDUIT SIZE	CDT CODE	VOLUME CM³

	22	PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED		
DIMENSIONAL RANGE (MM) FROM TO	> 0 20 > 20 30 > 30 70 > 70 100 > 100 150 > 150 200 > 200 250 > 250 300	CHART E1 300 400 400 500 500 600 600 700 700 800
TOLERANCE UNLESS OTHERWISE SPECIFIED		
±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2		

LINE DRAWN THROUGH A PART NUMBER	
PHYSICAL PART PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT DELPHI SALES TO ASSURE AVAILABILITY OF PARTS.	
DMD TYPE	
PART DRAWING	
STYLE	
VOLUME (LEFT)	DISTR CODE
SEE CHART	D
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH IEEE 1181/59-1994 AS AMENDED BY THE ISO GLOBAL DIMENSIONING AND FITTING (ISO/DIN 3301). SEPARATE PATENTING OF FEATURES MAY BE GRANTED SEPARATELY, REGARDLESS OF DATA REPRESENTATION.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE	DO NOT SCALE
PROJECTION	USE MATH
	
	

DELPHI

DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE

Chennai, India

COPYRIGHT 1995 DELPHI CORPORATION AND/OR ITS AFFILIATE
ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION
AND IS CONTAINING DELPHI CONFIDENTIAL INFORMATION.
THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF
THIS DOCUMENT OR ITS RELATED C/D WITH
OR AS COMMODATION OF ANY CONTENT TO OTHERS,
WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

					DATE	
DR						
APVD1	KANNAN AYYAPPARAJ				04NO15	
APVD2	KANNAN AYYAPPARAJ				04NO15	
APVD3	SUCHA SIAN				04NO15	
APVD4						
APVD5						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 1040001						
MATERIAL POLYAMIDE COMPOUND BLACK						
DRAWING NAME						
TAXI COV WIRE DRESS						
DRAWING NUMBER						
33299380						
SIZE	SCALE	FRAME NO	SHEET NO	STG		REV