






- 주 기 -


- 1. 사용상 유해한 흠, BURR등이 없을 것.
- 2. 명시되지 않은 R은 0.3이하로 할 것.
- 3. MARKING 및 형번은 당사규격에 준하여 각인할 것.
- 4. 명시되지 않은 공차는 일반공차에 준할 것.

△A 5. 금 도금 표시 부위( , 금도금 사양일 경우에만 적용)


△1 6. APTIV Drawing No : 35353569




SECTION A-A




SECTION B-B



SECTION C-C



SECTION D-D



GENERAL TOLERANCE							
일반공차 및 적용규격							
	10 MAX 10 이하	50 MAX 10 초과 50 이하	100 MAX 50 초과 100 이하	150 MAX 100 초과 150 이하	200 MAX 150 초과 200 이하	200 VR 200 초과	ANGLE
A	±0.2	±0.3	±0.5	±0.8	±1.0	±1.4	±30'
B	±0.3	±0.5	±0.8	±1.0	±1.4	±2.0	±30'
C	±0.5	±0.8	±1.0	±1.4	±1.6	±2.0	±1°

AVS, AVSS 0.5~0.85 AV 0.5	1.6	0.6	4.3	2.5	4.5	2.8	Au도금	TML 62Z-F-M-Au	MT095-33860	15484424	COPPER ALLOY			
AVS 0.2~0.3 AV, AVSS 0.3	1.5	0.45	4.1	2.1	4.3	2.2	Au도금	TML 62Z-F-S-Au	MT095-33060	15484423	COPPER ALLOY			
AVS, AVSS 0.5~0.85 AV 0.5	1.6	0.6	4.3	2.5	4.5	2.8	Sn도금	TML 62Z-F-M	MT095-33880	13677827	COPPER ALLOY			
AVS 0.2~0.3 AV, AVSS 0.3	1.5	0.45	4.1	2.1	4.3	2.2	Sn도금	TML 62Z-F-S	MT095-33080	15484425	COPPER ALLOY			
적용전선	R2	R1	W2	W1	H2	H1	표면처리	KUM PART NAME	KUM P/No.	APTIV P/No.	MATERIAL			
상 이 란								THIRD ANGLE PROJECTION	A	1/1	KKL	LJW	KNJ	CJW
									TOLERANCE	SCALE	DESIGN	DRAWN	CHECKED	APPROVED

-	19.07.19	-	△1	ADDED APTIV P/No.	LJW
CJW	14.05.30	E014-018	△A	금도금 사양 추가(4개소)	LJW
승인	DATE	NOTE No.	△	신 규	LJW
ALTERATION					담당
DRAWING NAME					TML 62Z-F-S
DRAWING No.					MT095-33080-C01
● APTIV ●					