






TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 101




SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	6
	LAST NO. USED	4

MISSING SYMBOLS
NO MISSING
SYMBOL NUMBER

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	1	
DATE	STG	REV	N/P	CHG					APVD	APVD
29MY08	R	01	-	-		ADDED PART 13699661 TO TAXI DWG; 13713662 - RELEASED	404812	JS	JS	SFM
220C08	R	02	-	-		ALL PARTS - PROCESS DIM WAS 1 & REVISED DIMS (3)PLCS	406497	TAI	TAI	SFM




SCALE 2:1



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- 13699661 USED IN ASSEMBLIES 13658062 & 13658063.
13713662 USED IN ASSEMBLY 13713668.
- THESE PARTS ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
CONNECTOR 13699658 & 13699659
TERMINAL 13543114
CABLE SEAL 13699664
- (1)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED".
- THESE PRODUCTS ARE NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR
IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR
BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE
FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER NAP 4.10-18.



13713662	01	AA	-	POLYAMIDE COMPOUND GRA LT	102	3,9,10,14,16,17	1.436
13699661	01	AB	-	POLYAMIDE COMPOUND BLUE	101	1-18	1.160
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	TYPE	OPEN CAVITIES	VOLUME

DIMENSIONAL RANGE (MM)										CHART	ET
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	
TO	20	30	70	100	150	200	250	300	400		
TOLERANCE UNLESS OTHERWISE SPECIFIED											
[±0.15] [±0.2] [±0.3] [±0.4] [±0.5] [±0.6] [±0.8] [±1] [±1.2]											
ANGULAR TOLERANCE ±2°											

2	PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	

DWG TYPE		PART DRAWING	
STYLE		VOLUME (CM³)	
SEE CHART		DISTR CODE	
		UNLESS OTHERWISE SPECIFIED	
		THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS		THIRD ANGLE PROJECTION	
REFERENCE		DO NOT SCALE	
		USE MATH DATA	

DELPHI		DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH	
DR		DATE	
APVD1 JOE SUDIK		29MY08	
APVD2 JOE SUDIK		29MY08	
APVD3 SEAN MILLER		29MY08	
APVD4			
APVD5			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10945001			
MATERIAL SEE CHART			
DRAWING NAME		TAXI LOCK STR RLFLPG	
DRAWING NUMBER		13713663	
SIZE	SCALE	FRAME NO	SHEET NO
A1	5:1	1 OF 1	1 OF 1
STG	REV	N/P	
R	02	-	