









SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL □ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	27
	LAST NO. USED	20

MISSING SYMBOLS		DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APVD	1	2		
		DATE	STG	REV	N/P								CHG	
NO MISSING SYMBOL NUMBER		30JUL02	R	05	-	-	CLEARED REV COLUMN: ALL PARTS - UPDATED PDM ATTRIBUTES	226419	ECB	JAA	TTP			
		21JUL03	R	06	-	-	ALL PARTS - ADDED TERMINAL MAKE STRAIGHTNESS AND TERMINAL CRIMP STRAIGHTNESS VIEWS.	242518	BRB	BRB	MC			
		04OCT04	R	07	-	-	-	ALL PARTS - ADDED STAMP DIE I.D.	259308	JPB	JVM	MM		
		01DEC08	R	08	-	-	-	ALL PARTS - UPDATED MAT'L CALLOUT	406833	MH	PYP	MH		
		30MR10	R	09	-	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	410250	FRE	FRE	VMR		
		16AUG10	R	10	-	-	-	ALL PARTS - ADDED PLATING NOTE, UPDATED MAT'L CALLOUT AND ADDED CONTACT AREA & CRIMP AREA COLUMNS ON CHART	411639	ESC	ESC	VMR		
		06OCT10	R	11	-	-	-	ALL PARTS - UPDATED PLATING NOTES	412129	CBG	CBG	VMR		
		23AUG11	R	12	-	-	-	ALL PARTS - ALTERNATIVE MAT'L SIZE WAS MAT'L SIZE AND ADDED PREFERRED MAT'L SIZE COLUMN	415183	AGM	JVM	OAF		
		19OCT16	R	13	-	-	-	ALL PARTS - OBSOLETE AND ADDED REPLACED BY COLUMN	434568	APB	APB	LES		
		07MAY18	R	14	-	-	-	33340450-51 - WERE ON TAXI DRAWING 33357482 SHEET011; ADDED 'REPLACED BY' COLUMN; REMOVED 'PLATED PREFORM' COLUMN & 'REPLACES' INFO; UPDATED PART AVAILABILITY AND RESTRICTED; 15373402-03 - REINSTATED; ADDED CROSSHATCH TO BLADE & 'PLATING' CALLOUT; REMOVED 'ALTERNATIVE MAT'L' COLUMN & 'REPLACED BY' INFO. REMOVED 'TYPE' COLUMN. ALL PARTS - ADDED 'AU' STAMP & DIM #20	439766	LB	LB	VMR		
		05JUN18	R	15	-	-	-	33340450-51 - UPDATED PART AVAILABILITY	440053	LB	LB	VMR		



SCALE 5:1



TWO RIB SEAL POSITION REFERENCE

SCALE 5:1

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- "*" DENOTES DIMENSIONS MADE AT CUT-OFF AND CRIMP DIE.
- MATING COMPONENTS OR EQUIVALENT: TERMINAL 15326426.
- PLATING TYPE:
 - GOLD OVER PALLADIUM AND NICKEL UNDERPLATE.
 - MATTE TIN ELECTROPLATE OVER NICKEL UNDERPLATE.

PLATING TYPE INFORMATION SHOWN ABOVE IS REFERENCE ONLY. PLATING REQUIREMENTS ARE CONTAINED IN APPLICABLE MATERIAL SPECIFICATION.

PART NO	REV	N/P	RESTRICTED USAGE	REPLACED BY	MAT'L SIZE	MATERIAL DESCRIPTION	SIZE (MM ²)	ID	DIA ±0.15	B ₁ ±0.2	(L)	APPLICATION	TYPICAL CABLE SEAL	TYPICAL SEALING CAVITY CONFIGURATION	CONTACT AREA PLATING TYPE (SEE NOTE 4)	CRIMP AREA PLATING TYPE (SEE NOTE 4)
33340450	02	AA	RESTRICTED	15373403	0.3 X 35.75	COPPER ALLOY	0.75 - 1	17	2.25 - 1.7	2.65	28.15	SEALED (GT)	12191227 OR EQUIVALENT	Ø 4 ROUND	I	II
33340451	02	AA	RESTRICTED	15373402	0.3 X 35.75	COPPER ALLOY	0.35 - 0.5	21	1.85 - 1.2	2.1	28.15	SEALED (GT)	12191226 OR EQUIVALENT	Ø 4 ROUND	I	II
15373403	03	-	-	-	0.3 X 35.75	COPPER ALLOY	0.75 - 1	17	2.25 - 1.7	2.65	28.15	SEALED (GT)	12191227 OR EQUIVALENT	Ø 4 ROUND	I	II
15373402	03	-	-	-	0.3 X 35.75	COPPER ALLOY	0.35 - 0.5	21	1.85 - 1.2	2.1	28.15	SEALED (GT)	12191226 OR EQUIVALENT	Ø 4 ROUND	I	II
PART NO	REV	N/P	RESTRICTED USAGE	REPLACED BY	MAT'L SIZE	MATERIAL DESCRIPTION	SIZE (MM ²)	ID	DIA ±0.15	B ₁ ±0.2	(L)	APPLICATION	TYPICAL CABLE SEAL	TYPICAL SEALING CAVITY CONFIGURATION	CONTACT AREA PLATING TYPE (SEE NOTE 4)	CRIMP AREA PLATING TYPE (SEE NOTE 4)

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT DELPHI SALES TO ASSURE AVAILABILITY OF PARTS.	
REVISED: 2018	
DWG TYPE PART DRAWING	
STYLE	
VOLUME (QAP)	DISTR CODE
UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE 2018 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2021. SEPARATE PATTERNING OF FEATURES MAY BE DIMED SEPARATELY. REPEL OF DATA REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	
DO NOT SCALE	
USE MATH DATA	
ANGULAR TOLERANCE 12°	

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE	
WARREN, OH	
COPYRIGHT 1999 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DATE	
DR	
APVD1 JOSE TAPIA	30NOV99
APVD2 PAUL MOYSEN	06DEC99
APVD3 MIKE J. DEMONICA	13DEC99
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 15349501	
MATERIAL SEE CHART	
DRAWING NAME TAXI TERM M GT 150 SEALED	
DRAWING NUMBER 15304703	
SIZE A0	SCALE 10:1
FRAME NO 1 OF 1	SHEET NO 3 OF 3
STG REV N/P	15 -