





①② MMC04F



ISO VIEW




SECTION A-A

- NOTE –
- 1. BEFORE USING, CHECK THE HARMFUL CRACK, BURR, ETC.
 - 2. MARKING & CAV.NO. BY AS A GENERAL RULE OF KUM.
 - 3. GENERAL TOLERANCES – SEE BLOW
 - 4. ASSY PART
 - 1) SIDE HOLDER : HK335-04030
 - 2) TERMINAL




APPLICATION WIRE(SQ)	KUM PART NAME	KUM P/No.	APTIV P/No.
CHFUS 0.22sq	TERMINAL MMC-F-SS	TK195-00400	35290158
AVSS 0.3~0.5sq	TERMINAL MMC-F-S	TK195-00100	13894953
CHFUS 0.22sq	TERMINAL MMC-F-SS-Au	TK195-00410	35296430
AVSS 0.3~0.5sq	TERMINAL MMC-F-S-Au	TK195-00110	35296429

1 5. APTIV Drawing No : 35352462

③ S/H MMC04F-GN



ISO VIEW



GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	150MAX	200MAX	200VR	ANGLE
A	±0.2	±0.3	±0.5	±0.8	±1.0	±1.4	±0.5도

③ S/H MMC04F-GN						
②	MMC04F-W	HK325-04010	35297650	WHITE	PBT	
①	MMC04F-B	HK325-04020	35297651	BLACK	PBT	
No.	KUM PART NAME	KUM P/No.	APTIV P/No.	COLOR	MATERIAL	
	THIRD ANGLE PROJECTION	A	-	JJS	JJS	KDK CJW
	TOLERANCE	SCALE	DESIGN	DRAWN	CHECKED	APPROVED

	19.07.09	-	1	ADDED APTIV P/No.	JJS
CJW	13.02.20	E013-0034	A	CHANGE SHAPE(3POINT)	JJS
CJW	11.10.17	E011-0135	-	RELEASED	JJS
APVD	DATE	NOTE No.	SYM	ALTERATION	DWN

DRAWING NAME	MMC04F-B
DRAWING No.	HK325-04020-C01

