






- △A△B - NOTE -
- 1. BEFORE USING, CHECK THE HARMFUL CRACK, BURR, ETC.
 - 2. MARKING & CAV No. BY AS GENERAL RULE OF KUM.
 - 3. GENERAL TOLERANCES - SEE BELOW.
 - 4. Au-Plated PARTS.(OPTIONAL Au-Plated CASE)
 - 5. APPLICATION CONNECTOR : HSC CONN. RECEP.
 - △i 6. APTIV Drawing No : 35357028



SECTION B-B



SECTION A-A



SECTION C-C

GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	150MAX	200MAX	200VR	ANGLE
A	±0.2	±0.3	±0.5	±0.8	±1.0	±1.4	±30°

AVSS 0.3~0.5sq	2.0	2.0	A 2.4	A 2.5	0.6	0.7	Au도금	HSC-F-S-Au	TK105-00110	35296416	Copper Alloy(t=0.2)			
AVSS 0.3~0.5sq	2.0	2.0	A 2.4	A 2.5	0.6	0.7	Sn도금	HSC-F-S	TK105-00100	13965510	Copper Alloy(t=0.2)			
CHFUS 0.22sq	1.5	1.5	2.2	2.3	0.6	0.7	Au도금	HSC-F-SS-Au	TK105-00410	35296418	Copper Alloy(t=0.2)			
CHFUS 0.22sq	1.5	1.5	2.2	2.3	0.6	0.7	Sn도금	HSC-F-SS	TK105-00400	35296417	Copper Alloy(t=0.2)			
적용전선	Wa	Ha	Wb	Hb	Ra	Rb	표면처리	KUM PART NAME	KUM P/No.	APTIV P/No.	MATERIAL			
TABLE								THIRD ANGLE PROJECTION	A	-	KHL	KHL	KDK	CJW
									TOLERANCE	SCALE	DESIGN	DRAWN	CHECKED	APPROVED

CJW	19.05.10	-	△1	ADDED APTIV P/No.	JJS
CJW	13.08.12	E013-0197	△B	CHANGED SHAPE & NOTE(5POINT)	JJS
CJW	09.05.14	E009-0052	△A	CHANGED SHAPE & NOTE(8POINT)	KHL
CJW	08.11.19	E008-0291	△-	RELEASED	KHL
APVD	DATE	NOTE No.	SYM	ALTERATION	DWN
DRAWING NAME					TERMINAL HSC-F-SS
DRAWING No.					TK105-00400-C01
● APTIV ●					