



PLASTIC HOOD LOCKING
WITH METAL PART


SECTION B-B



ALL 4 LOCKS
MUST BE CLIPPED






SECTION A-A





NOTE

- TEMPERATURE CLASS RANGE -40 TO 170° C; VIBRATION CLASS 1
- CRIMPING SPEC APTIV FE CS 25 001;
- PRODUCT SPECIFICATION: FEPS 25-014
- TERMINAL MAX. ENGAGE FORCE WHEN MATING WITH GAUGE Ø 12: 45N MAX



REP	APTIV		CRIMP SIZE (mm²)	ASS P/N	
	REF. P/N	REV.		35454328	35443592
1	35454324	02	35-60	X	
	35443594	02	70-95		X
2	35443595	02	/	X	X

APTIV		CRIMP SIZE (mm²)				MATERIAL		FINISH		WEIGHT (g)
REF. P/N	REV.		A ± 0.7	B ± 0.6	C ± 0.5	CONTACT PART:	PLASTIC HOOD:	CONTACT PART:		
35454328	02	35-60	16.45	17.65	4.37	COPPER ALLOY	PA66 GF30 (BLACK)	Ag		26.59
35443592	02	70-95	19.95	22.71	5.50					28.46



DIM TO CHECK COTES A VERIFIER		DIMENSIONAL RANGE (MM)		CHART D
() DIM FOR HELP COTES POUR INFO		FROM	0	> 12
		TO	12	
THEORETIC DIM COTES THEORIQUES		TOLERANCE UNLESS OTHERWISE SPECIFIED		
			±0.1	±0.2
		ANGULAR TOLERANCE ±2°		