





SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	52
	LAST NO. USED	35


MISSING SYMBOLS		DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APVD	P/NO 1 2
DATE	STG	REV	N/P	CHG							
NO MISSING SYMBOL NUMBER	02MY02	R	02	-	-		CLEARED REVISION COLUMN: 15436718 AND 15436720 - RELEASED	224587	LOA	JAA	EH
	14JN05	R	03	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES	260551	JS	JS	QR
	20JUL05	R	04	-	-		ALL PARTS - ADDED SURFACE FLASH NOTE	270013	MM	MM	LN
	20SE05	R	05	-	-		15436718 & 15436720 - INACTIVE; 15366040 AND 15423592 - REMOVED RECESSED AREA IN WIRE END OF CAVITY	272769	RH	RH	BER
	30MY06	R	06	-	-		15436718 & 15436720 - REINSTATED AND REMOVED RECESSED AREA IN WIRE END OF CAVITY; ALL PARTS - REVISED NOTE 2 CAVITY PLUG WAS 15305169	281066	RMG	JAA	PYP
	12DE07	R	07	-	-		ALL PARTS - ADDED APPLICATION DATA NOTE, APPEARANCE ITEM NOTE & RECYCLING CODE LABEL, REMOVED PART ACCEPTS NOTE AND REVISED MAT'L CALLOUT TO GENERIC CALLOUT	403153	JTZ	EVV	JGS
	27JN08	R	08	-	-		ALL PARTS - ADDED DIMS (2 PLCS)	405195	MDH	FRG	JDS
	11OC12	R	09	-	-		ALL PARTS - ADDED PERFORMANCE REQUIREMENT NOTE; 15436718 & 15436720 - INACTIVE, RESTRICTED AND ADDED REPLACED BY INFO	419998	KYT	JAA	DGL




TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN






TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 101



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE PER ISO 11469. (1.15) X (0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
- (1.63) X (0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.
- FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
- THIS CONNECTION MEETS OR EXCEEDS SAE/USCAR-2 AUGUST 1997, SECTION 5.3.1.2, TERMINAL DISENGAGE CRITERIA WITH THE APPLICATION OF A TERMINAL POSITION ASSURANCE (TPA) SECONDARY LOCK.

15436720	03	AC	104	B AND D	2.041	RESTRICTED	15366028
15436718	03	AC	103	A AND C	2.041	RESTRICTED	15366026
15423592	03	AD	102	A AND D	2.041	-	-
15366040	04	AD	101	-	2.040	-	-
PART NO	REV	N/P	TYPE	BLOCKED CAVITIES	VOLUME (CM ³)	RESTRICTED USAGE	REPLACED BY

13 PROCESS SENSITIVE DIMENSION						REFERENCE	
DIMENSIONS ENCLOSED IN $\square$ INDICATE TOLERANCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED							
DIMENSIONAL RANGE (MM)						CHART E1	
FROM	TO	> 0	> 30	> 70	> 100	> 150	> 200
0	20	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8
20	100	±0.3	±0.4	±0.5	±0.6	±0.8	±1.0
100	200	±0.4	±0.5	±0.6	±0.8	±1.0	±1.2
200	300	±0.5	±0.6	±0.8	±1.0	±1.2	±1.5
300	400	±0.6	±0.8	±1.0	±1.2	±1.5	±2.0
TOLERANCE UNLESS OTHERWISE SPECIFIED							
±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1.2
ANGULAR TOLERANCE $\pm 2^\circ$							
						THIRD ANGLE PROJECTION	
						DO NOT SCALE	
						USE MATH DATA	