






TYPE 402
SAME AS TYPE 101
EXCEPT AS SHOWN




16X 17
16X 2.82 ±0.4 TYP




RECOMMENDED MATING PCB LAYOUT

SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.		TOTAL NO OF INSPECTIONS REQUIRED	
LAST NO. USED		30	


DATE	STG	REV	N/P	CHG	ZONE	REVISION HISTORY	AUTH	DR	APP	2
09JAO2	R	01	-	-	-	ALL PARTS - RELEASED	217513	J.L.J.	J.L.J.	DM
02AP02	R	02	-	-	-	ALL PARTS - UPDATED REVISED CONNECTOR	222783	END	END	DM
29SE03	R	03	-	-	-	UPDATED PART TABLE, REMOVED DIMENSIONS SHOWN ON ESD DETAILS, REVISED NOTES.	246228	M.M.M.	M.M.M.	DM
18DE03	R	04	-	-	-	ADDED DIM 11 (PLC)	248829	ECB	AUG	DM
15SE04	R	05	-	-	-	ALL PARTS - UPDATED FORMAT AND REMOVED N/P COLUMN FROM CHART	258905	BRB	BRB	DM
31JA05	R	06	-	-	-	13518952 - RELEASED	264136	LMB	LMB	DM
20JN05	R	07	-	-	-	13533636 - RELEASED	269339	RH	RH	DM
14OC05	R	08	-	-	-	15423735 - OBSOLETE AND ADDED NOTE	272462	PCP	PCP	DM






TYPE 403
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 404
SAME AS TYPE 101
EXCEPT AS SHOWN




TYPE 401



TYPE 405
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 406
SAME AS TYPE 101
EXCEPT AS SHOWN



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - MATING INTERFACE AND PRINTED CIRCUIT BOARD INTERFACE ARE VERIFIED BY APPROVED GAGES FOR FUNCTIONAL FIT PER CONTROL PLAN.
 - SEE PART NUMBER TABLE FOR ESD INSPECTION PRINT NUMBER.
 - REFERENCE MATING COMPONENTS OR EQUIVALENT: SEE CHART

PART NO	REV	N/P	STATUS	TYPE	DESCRIPTION	CONFIG	USCAR TYPE	COLOR	MODULE 1	REV	CONNECTOR	MATING CONNECTOR	REPLACED BY
15423739	01	AD		406	16M	STRAIGHT	16F	NAT	ESD30452 INDEX F	01	15421764	15394154	-
15423738	01	AD		405	16M	STRAIGHT	16E	DK BLU	ESD30452 INDEX E	01	15421763	15394153	-
15423737	01	AD		404	16M	STRAIGHT	16D	GRN	ESD30452 INDEX D	01	15421762	15394152	-
15423736	01	AD		403	16M	STRAIGHT	16C	BRN	ESD30452 INDEX C	01	15421761	15394151	-
15423735	01	AE	OBSOLETE	402	16M	STRAIGHT	16B	GRA	ESD30452 INDEX B	01	15421760	15394149	15496639
15423734	01	AD		401	16M	STRAIGHT	16A	BLK	ESD30452 INDEX A	01	15421759	15394150	-
13533636	01	-	RESTRICTED	401	16M	STRAIGHT	16A	GRA	ESD30452 INDEX A	01	13533635	15394150	-
13518952	01	-		401	16M	STRAIGHT	16A	BLK	ESD30452 INDEX A	01	13518951	15394150	-

DELPHI
DELPHI PACKARD ELECTRIC SYSTEMS
WARREN, OH

DWG TYPE: PART DRAWING

STYLE: 1D

VOLUME (CM): 1D

UNLESS OTHERWISE SPECIFIED:
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994
ALL DIMENSIONS ARE TO FACE UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

(N/A) PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE
DIFFERENCE BETWEEN DIMENSION AND TOLERANCE
LIMITS ARE ESTABLISHED

THIRD ANGLE
PROJECTION

DO NOT
SCALE

USE MATH
DATA

DELPHI

DELPHI
DELPHI PACKARD ELECTRIC SYSTEMS
WARREN, OH

DWG TYPE: PART DRAWING

STYLE: 1D

VOLUME (CM): 1D

UNLESS OTHERWISE SPECIFIED:
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994
ALL DIMENSIONS ARE TO FACE UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

(N/A) PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE
DIFFERENCE BETWEEN DIMENSION AND TOLERANCE
LIMITS ARE ESTABLISHED

THIRD ANGLE
PROJECTION

DO NOT
SCALE

USE MATH
DATA

DELPHI

21753421