

| PART NUMBER      |                       |                  |                       |          |    | GRIP CODE | WIRE SIZE | CONDUCTOR CH (SECT Z-Z, +/-0.05) | CONDUCTOR CW (SECT Z-Z, +/-0.10) | INSULATION CH (SECT Y-Y, +/-0.10) | INSULATION CW (SECT Y-Y, +/-0.10) |
|------------------|-----------------------|------------------|-----------------------|----------|----|-----------|-----------|----------------------------------|----------------------------------|-----------------------------------|-----------------------------------|
| TIN ALL OVER     | PALLADIUM             |                  | GOLD                  |          |    |           |           |                                  |                                  |                                   |                                   |
| AREA 1 (IN-LINE) | AREA 2 (SHORTING BAR) | AREA 1 (IN-LINE) | AREA 2 (SHORTING BAR) |          |    |           |           |                                  |                                  |                                   |                                   |
| 54001626         | 54001628              | 54001629         | 54001633              | 54001634 | 16 |           | 1.20      | 2.05                             | 2.45                             | 2.60                              |                                   |
|                  |                       |                  |                       |          | 18 |           | 1.15      | 2.05                             | 2.15                             | 2.60                              |                                   |
| 54002001         | 54002003              | 54002004         | 54002008              | 54002009 | 20 |           | 1.05      | 1.65                             | 2.00                             | 2.40                              |                                   |
|                  |                       |                  |                       |          | 22 |           | 0.95      | 1.65                             | 1.60                             | 2.40                              |                                   |





TABLE 2 - PLATING DETAILS

| MATERIAL                    | PLATING TYPE/PROCESS                                                                 | THICKNESS                                                               | APPLICABLE SPEC.     | PLATING AREA     |
|-----------------------------|--------------------------------------------------------------------------------------|-------------------------------------------------------------------------|----------------------|------------------|
| TYPE 1<br>TIN               | 100% ELECTROMATTE TIN                                                                | 0.0012 - 0.0026                                                         | NONE                 | ALL OVER         |
| TYPE 2<br>PALLADIUM OR GOLD | a) SULFAMATE DUCTILE NICKEL                                                          | 0.00127 - 0.0025 (MEASURED AT POINT N FOR AREA 2, 3)                    | ASTM B 689-90 TYPE 2 | #3               |
|                             | b) NICKEL FLASH                                                                      | 0.000127 MAX                                                            | ASTM B 689-90 TYPE 2 | #4               |
|                             | c) 100% PURE ELECTROMATTE TIN (POST PLATED)                                          | 0.0012 - 0.0026                                                         | NONE                 | #4               |
|                             | d) PALLADIUM OPTION GOLD FLASH - 99% PURE PER ASTM B488 TYPE 2 CODE C OVER PALLADIUM | PD - 0.000508 MIN AU - 0.000051 MIN (MEASURED AT POINT N FOR AREA 2, 3) | ASTM B 488-95        | #1 OR #2 SEE P/N |
|                             | e) GOLD OPTION GOLD 99% PURE PER ASTM B488 TYPE 2 CODE C                             | AU - 0.00076 MIN (MEASURED AT POINT N FOR AREA 2, 3)                    | ASTM B 488-95        | #1 OR #2 SEE P/N |

PLATING NOTES:

- TIN PLATE NOT TO OVERLAP PRECIOUS METAL
- TIN AND NICKEL OVERLAP IS NECESSARY TO AVOID EXPOSURE OF BARE METAL



CRIMP TOOL INFORMATION (REF. ONLY)

TABLE 3 - TERMINAL GRIP / CRIMP TOOL DIMENSION TABLE (CRIMP TOOL DIMENSIONS (E-T) FOR REFERENCE ONLY)

| PART NUMBER      |                       |                  |                       |          |    | GRIP CODE            | WIRE SPECIFICATION | A   | B   | (ØC1) | C2  | (ØD1) | D2  | E +/- 0.02 | F +/- 0.02 | G +/- 0.02 | J +/- 0.02 | K +/- 0.02 | M +/- 0.02 | N +/- 0.02 FOR "O" STYLE | N +/- 0.02 FOR "D" STYLE | P +/- 0.02 FOR "D" STYLE | P +/- 0.02 FOR "O" STYLE | R +/- 0.02 | S +/- 0.02 | T +/- 0.02 |
|------------------|-----------------------|------------------|-----------------------|----------|----|----------------------|--------------------|-----|-----|-------|-----|-------|-----|------------|------------|------------|------------|------------|------------|--------------------------|--------------------------|--------------------------|--------------------------|------------|------------|------------|
| TIN ALL OVER     | PALLADIUM             |                  | GOLD                  |          |    |                      |                    |     |     |       |     |       |     |            |            |            |            |            |            |                          |                          |                          |                          |            |            |            |
| AREA 1 (IN-LINE) | AREA 2 (SHORTING BAR) | AREA 1 (IN-LINE) | AREA 2 (SHORTING BAR) |          |    |                      |                    |     |     |       |     |       |     |            |            |            |            |            |            |                          |                          |                          |                          |            |            |            |
| 54001626         | 54001628              | 54001629         | 54001633              | 54001634 | 16 | ESB-MIL123-A/MS 8289 |                    | 3.0 | 3.7 | 1.00  | 1.6 | 1.75  | 2.4 | 0.92       | 0.53       | 0.13       | 2.56       | 1.99       | 1.97       | 0.18                     | 0.67                     | 2.34                     | 1.15                     | 2.52       | 2.53       | 1.23       |
| 54002001         | 54002003              | 54002004         | 54002008              | 54002009 | 20 | ESB-MIL123-A/MS 8288 |                    | 2.5 | 3.1 | 0.76  | 1.4 | 1.40  | 2.0 | 0.74       | 0.43       | 0.09       | 2.06       | 1.59       | 1.59       | 0.16                     | 0.60                     | 2.16                     | 1.10                     | 2.33       | 2.33       | 1.17       |

CRIMP NOTES:

- THE CRIMP AND CRIMP TOOLING DIMENSIONS HAVE BEEN ESTABLISHED AND VALIDATED TO USCAR-21 USING FCI TOOLS, MACHINES AND PROCESSES. THE DIMENSIONS SHOWN ARE FOR REFERENCE.
- WIRING SUPPLIERS ARE TO DEVELOP AND VALIDATE THEIR CRIMPING SPECIFICATIONS AND PROCESSES ACCORDING TO ALL ASPECTS OF USCAR-21 REV. 2. NOTE THAT AS STATED IN USCAR-21, WIRING SUPPLIER DEFINED CRIMPING SPECIFICATIONS AND CRIMPING PROCESSES MAY IMPACT CONNECTOR FUNCTIONS. (SEE USCAR-21 REV. 2, 4.2.5.1); CONTACT FCI ENGINEERING FOR ANY NEEDED ASSISTANCE IN THIS REGARD.
- DESIGN REFERENCE INFORMATION: IT IS RECOMMENDED THAT THE NOTED NOMINAL OFFSET BETWEEN THE CONDUCTOR GRIP AND INSULATION GRIP NOT BE CHANGED BY THE CRIMPING PROCESS. RESIZING THIS FEATURE DURING CRIMPING CAN NEGATIVELY IMPACT CONNECTOR SYSTEM FUNCTION. ACCEPTABILITY OF THE ACTUAL NOTED CRIMPED OFFSET CRIMPING SPECIFICATION, AND CRIMPING PROCESS USED IS TO BE DETERMINED AS DEFINED IN CRIMP NOTE 2.
- DESIGN REFERENCE INFORMATION: CRIMPED TERMINALS ARE USED ON VARIOUS CONNECTOR APPLICATIONS. NORMALLY, FOR DESIGN PURPOSES, A CONDUCTOR AND INSULATION CRIMP ANGLE TOLERANCE OF +/- 3 DEGREES RELATIVE TO TERMINAL DIRECTION "E" CAN BE ASSUMED. ACTUAL CRIMP TOLERANCES DEFINED WITHIN A HARNESS MAKER'S CRIMPING PROCESS FOR A SPECIFIC CONNECTOR APPLICATION MUST BE VERIFIED AS SUITABLE BY FULL VALIDATION TO ALL ASPECTS OF USCAR-21 INCLUDING SECTION 4.2.5.

|             |   |          |    |    |          |    |    |          |          |
|-------------|---|----------|----|----|----------|----|----|----------|----------|
| 54001633    | L | 13768448 | 01 | AM | 15520260 | 01 | AF | M6575H94 | M6575S90 |
| 54002008    | L | 13783476 | 01 | AL | 15520262 | 01 | AF | M6575H94 | M6575S90 |
| 54002004RWA | L | 15520259 | 01 | AE | -        | -  | -  | 33500641 | -        |
| 54002004    | L | 33500641 | 01 | AF | 15520262 | 01 | AF | M6575H94 | M6575S90 |
| 54002003RWC | L | 15520257 | 01 | AE | -        | -  | -  | 13851003 | -        |
| 54002003RWA | L | 15548865 | 01 | AC | -        | -  | -  | 13851003 | -        |
| 54002003    | L | 13851003 | 01 | AJ | 15520262 | 01 | AF | M6575H94 | M6575S90 |
| 54002001RWA | L | 15520256 | 01 | AE | -        | -  | -  | 13624759 | -        |
| 54002001    | L | 13624759 | 01 | AL | -        | -  | -  | M6576H94 | M6576S90 |
| 54001629    | L | 13755243 | 01 | AK | 15520260 | 01 | AF | M6575H94 | M6575S90 |
| 54001628RWA | L | 15548863 | 01 | AC | -        | -  | -  | 13795935 | -        |
| 54001628    | L | 13795935 | 01 | AF | 15520260 | 01 | AF | M6575H94 | M6575S90 |
| 54001626RWC | L | 33162170 | 01 | AC | -        | -  | -  | 13630404 | -        |
| 54001626RWA | L | 15520254 | 01 | AE | -        | -  | -  | 13630404 | -        |
| 54001626    | L | 13630404 | 01 | AM | -        | -  | -  | M6576H94 | M6576S90 |

| PART NO | REV | PLATED | UNPLATED | MAT'L SPEC | ALTERNATIVE MAT'S SPEC |
|---------|-----|--------|----------|------------|------------------------|
| MVL     | 9   |        |          | APTIV      |                        |

