







MISSING SYMBOLS	DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APD/APVD	
	DATE	STR	REV	N/P					CHG	1
NO MISSING SYMBOL NUMBER	19NO03	R	03	-	-	ALL ACTIVE PARTS - CLEARED REV COLUMN; REDRAWN TO PD AND UPDATED PDM ATTRIBUTES	247796	JTV	FKV	RMD
	21NO05	R	04	-	-	02977112, 02962718, 02965400, 02962543, 12010566, 12010769, 12015010 & 12052489- ADDED WING CONSTRUCTION IIII VIEW	274984	CJP	CJP	EST
	08DE05	R	05	-	-	02977112, 02962718, 02965400, 02962543, 12010566, 12010769, 12015010 & 12052489- UPDATED WING CONSTRUCTION IIII	275486	CJP	CJP	EST
	25MY10	R	06	-	-	ALL ACTIVE PARTS - REVISED MAKE DIE SERIES NOTE, ADDED OPTIONAL CONSTRUCTION NOTE	410899	LHT	LHT	LHT
	14JAU15	R	07	-	-	02962718, 02977106, 02977369, 02984712, 12010769 & 12015010 - OBSOLETE	430437	LES	LES	WMP



NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA
2. "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE DIE
SERIES NUMBER (P01, P02, P03, ETC.).
OPTIONAL CONSTRUCTION COULD BE NOT "PXX" STAMP.
3. TO FIT .032 X .250 BLADE

				0.180 X 1.188		12052489	A	04	M1588AAE ▲						X	X	X	0.8 - 0.5	2.40 - 2.03	19	102	111	.140	.165			
				0.180 X 1.188		12046502	A	-	M1573058						X	X	X	0.8 - 0.5	3.13 - 2.03	19	104	111	.125	.195			
				0.180 X 1.188		12015010	B	06	M1588AAE ▲							X	X	(2) 0.8 - 0.5	2.40 - 2.03	(2) 19	106	111	.130	.250			
				0.180 X 1.188		12010771	B	02	M1588AAE						X	X	X	0.35 - 0.22	2.08 - 1.12	23	102	1	.090	.145			
				0.180 X 1.188		12010770	B	02	M1588AAE ▲						X	X	X	0.35 - 0.22	2.08 - 1.12	23	102	1	.090	.145			
				0.180 X 1.188		12016749	C	05	M1573058						X	X	X	(2) 0.35 - 0.22	2.08 - 1.12	(2) 23	101	111	.150	.215			
				0.180 X 1.188		12010566	C	04	M1588AAE ▲						X	X	X	0.8 - 0.5	2.40 - 2.03	19	102	111	.140	.165			
				0.180 X 1.188		08966236	A	-	M1573058						X	X	X	0.22	1.11 - 1.02	24	101	11	.100 - .080	.120 - .100			
12033824	E	02		0.180 X 1.188	M1403058											X	X	2.0 - 1.0	3.05 - 2.48	15	101		.140	.230			
02984712	CB	03		0.018 X 1.188	M1403058												X	2.0 - 1.0	3.05 - 2.48	15	101		.140	.185			
02964592	CC	-		0.018 X 1.188	M1403058										X	X	X	2.0 - 1.0	3.97 - 3.36	15	101		.140	.230			
02964313	CC	-		0.018 X 1.188	M1403058											X	X	2.0 - 1.0	3.97 - 3.36	15	101		.140	.230			
02984103	CD	-		0.018 X 1.188	M1403058	08917470	CD	-	M1573058						X	X	X	(2) 0.8 - 0.5	2.40 - 2.03	(2) 19	101		.190	.250			
02977938	CC	02		0.018 X 1.188	M1403058										X	X	X	0.8 - 0.5	3.13 - 2.69	19	101		.135	.185			
02975521	CC	-		0.018 X 1.188	M1403058					02977963	CC	-	V1403058			X	X	(2) 0.8 - 0.5	2.40 - 2.03	(2) 19	101		.135	.185			
02975520	CB	-		0.018 X 1.188	M1403058											X	X	0.8 - 0.5	2.40 - 2.03	19	101		.135	.175			
02977369	CB	04		0.018 X 1.188	M1403058	02977705	CB	03	M1573058							X	X	2.0 - 1.0	3.97 - 3.36	15	101		.140	.230			
02977106	CB	03		0.018 X 1.188	M1403058	02977375	CB	02	M1573058							X	X	0.8 - 0.5	3.13 - 2.69	19	101		.135	.185			
02977369	CC	02		0.018 X 1.188	M1403058	02977114	CC	02	M1573058							X	X	0.8 - 0.5	3.13 - 2.69	19	101		.135	.185			
02965199	CC	03		0.018 X 1.188	M1403058	02965511	CC	02	M1573058							X	X	2.0 - 1.0	3.97 - 3.36	15	101		.140	.230			
02965156	CC	-		0.018 X 1.188	M1403058	02965401	CC	03	M1573058							X	X	0.8 - 0.5	2.40 - 2.03	19	101		.135	.175			
02965952	CC	-		0.018 X 1.188	M1403058	02965728	CC	03	M1573058							X	X	2.0 - 1.0	3.05 - 2.48	15	101		.140	.185			
02968718	CD	05		0.018 X 1.188	M1403058	02977112	CD	04	M1573058							X	X	(2) 0.8 - 0.5	2.40 - 2.03	(2) 19	101	111	.190	.250			
02965873	CB	-		0.018 X 1.188	M1403058	02965867	CB	03	M1573058							X	X	2.0 - 1.0	3.05 - 2.48	15	101		.140	.185			
02962572	CB	02		0.018 X 1.188	M1403058	02965510	CB	03	M1573058							X	X	0.8 - 0.5	2.40 - 2.03	19	101		.135	.175			
02962543	CE	04		0.018 X 1.188	M1403058	02965400	CE	05	M1573058							X	X	(2) 0.8 - 0.5	2.40 - 2.03	(2) 19	105	111	.190	.250			
02962508	CC	02		0.018 X 1.188	M1403058	02965141	CC	03	M1573058							X	X	0.8 - 0.5	2.40 - 2.03	19	101		.135	.175			
02962447	CC	02		0.018 X 1.188	M1403058	02965142	CC	03	M1573058							X	X	2.0 - 1.0	3.05 - 2.48	15	101		.140	.185			
PART_NO	REV	N/P		MAT'L SIZE	MAT'L SPEC	PART_NO	REV	N/P	MAT'L SPEC	PART_NO	REV	N/P	MAT'L SPEC	PART_NO	REV	N/P	MAT'L SPEC	NIB	TANG	FOOT	SIZE (MM)	DIA (MM)	ID	TYPE	WING CONST	E _{0.015}	F _{0.015}
				UNPLATED			TIN PLATED			SILVER PLATED			FEATURES			CARB F											

A LINE DRAWN THROUGH A PART NUMBER
 INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE
 FOR ORDERING.
 PART NUMBERS THAT DO NOT HAVE A LINE PATTERN INDICATE
 THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.
 CONTACT DELPHI SALES TO ASSURE AVAILABILITY
 OF PARTS.

DMD TYPE PART DRAWING

STYLE

VOLUME 1001 DISTIR CODE

D

UNLESS OTHERWISE SPECIFIED
 THIS DOCUMENT IS IN ACCORDANCE WITH THE 154-58-1994
 IS MODIFIED BY THE FOLLOWING: 1. IDENTIFICATION
 INFORMATION REMAINS THE SAME. 2. IDENTIFICATION
 FEATURES MAY BE OBTAINED SEPARATELY, IRRESPECTIVE OF DATUM
 REFERENCES.

ALL DIMENSIONS ARE IN INCHES

DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH COPYRIGHT 2003 DELPHI CORPORATION AND/OR ITS AFFILIATES, ALL RIGHTS RESERVED. REVISED 2003 THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI'S CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED OR UNRELATED AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DR	DATE
APV01 J. LUIS TAPIA	19N003
APV02 FRANCESCO KOPCONA	19N003
APV03 RICHARD DICINTIO	19N003
APV04	
APV05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE CHRT	

() PROCESS POSITIVE DIMENSION DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED		REFERENCE	
DIMENSIONAL RANGE (IN) CHART J FROM 0 TO <50 >.500		THIRD ANGLE PROJECTION	DO NOT SCALE  USE MATH DATA
TOLERANCE UNLESS OTHERWISE SPECIFIED ±.005 ±.010 ANGULAR TOLERANCE 12°			
4		3	

DRAWING NAME							
TAXI TERM F 56 SERIES							
DRAWING NUMBER							
02962874							
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P	
A0	5:1	1 OF 1	1 OF 13	R	07	-	
2		1		1			