











SECTION B-B



TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN



SECTION A-A

NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR - SEE CHART
- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EANP-4-3-CS-01-EN.
- CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER THE LATEST REVISION OF ESD S1085201.
- WARPAGE IS PERMISSIBLE IN THE AREA OF LEGS; MAX 2.0 MM
- PART CAN BE RESTRICTED WITH FIXTURE TO BE MEASURED

33377052	04	AC	102	POLYAMIDE COMPOUND GRAY LT	33297515 / 33371910	10.149	35294083
33377051	04	AC	101	POLYAMIDE COMPOUND NATURAL	33297514 / 33371909	10.168	35294082
PART NO	REV	N/P	TYPE	MATERIAL SPECIFICATION AND COLOR	MATING	VOLUME (CM ³)	REPLACED BY

DIMENSIONAL RANGE (MM)										CHART E	
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	
TO	20	30	70	100	150	200	250	300	400		
TOLERANCE UNLESS OTHERWISE SPECIFIED											
	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2		
ANGULAR TOLERANCE ±2°											