

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

©

COPYRIGHT — By —

LOC

DIST

REVISIONS

AF

50

P

LTR

DESCRIPTION

DATE

DWN

APVD


A1

RELEASED PER ECO 11-018653

13SEP11

JR

PD






1 CONTINUOUS STRIP ON REELS


2 WIRE SIZE IS 500-1900 CMA,
0.6-1.1mm DIA., SINGLE WIRE
CRIMP WIDTH IS 1.78 [.070], F TYPE3 INSULATION RANGE 2.54-3.05 [.100-.120] DIA.
CRIMP WIDTH IS 3.56 [.140], OVERLAP TYPE

4 0.002032 [.00080] MIN TIN PLATE

5 MATING TAB THK IS 0.81±0.025 [.032±.001].



SECTION A-A



SECTION B-B

1742881-1

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN jr_ruth 08DEC10

CHK PETE DESANTIS 08DEC10

APVD PETE DESANTIS 08DEC10

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING

STE

TE Connectivity

NAME

RECEPTACLE, FASTON, FLAG,
AMPLIVAR, 6.35 [.250] SERIES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3


00779

C-1742881

SCALE 5:1

SHEET 1 OF 1

REV A1

DIMENSIONS:
MM [INCHES]TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± —
1 PLC ± —
2 PLC ± 0.25 [.010]
3 PLC ± —
4 PLC ± —
ANGLES ± 5°
FINISH

MATERIAL

4M BRASS

