


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISER PER ECN-21-105646	09JUN2021	RZ	WK


	-	9.50	19.40	6.00	6.70	8.70	10.00	10.50	CT125		5-1814821-7
OBSOLETE	-	9.50	19.40	6.00	6.70	8.70	10.00	10.50	CT125		5-1814821-6
OBSOLETE	9-1478243-0	8.50	19.40	4.85	5.70	7.70	9.00	9.50	CT100		5-1814821-5
OBSOLETE	9-1478243-0	8.50	19.40	4.85	5.70	7.70	9.00	9.50	CT100		5-1814821-4
	1583581-1	10.20	19.40	4.85	5.50	9.50	10.80	11.20	RG6/U		5-1814821-3
OBSOLETE	1583581-1	10.20	19.40	4.85	5.50	9.50	10.80	11.20	RG6/U		5-1814821-2
	9-1478243-0	8.50	20.40	3.90	4.70	7.50	9.00	9.50	RG59B/U, 62A/U, 140/U, 210/U, URM90, Belden 9291, 9291, KX6A, KX25, KX52, KX53		5-1814821-1
OBSOLETE	9-1478243-0	8.50	20.40	3.90	4.70	7.50	9.00	9.50	RG59B/U, 62A/U, 140/U, 210/U, URM90, Belden 9291, 9291, KX6A, KX25, KX52, KX53		5-1814821-0
	DIE SET	G	F	E	D	C	B	A	CABLE GROUPS		PART NO.
DIMENSIONS											

NOTES


- 1 SINGLE PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Ni PLATING
4. HAND TOOL: 9-1478240-0
5. FOR TECHNICAL DATA REFER TO YOUR LOCAL TE CONNECTIVITY SALES OFFICE
6. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



RECOMMENDED
CABLE STRIPPING DIM'S



RECOMMENDED CRIMP
OUTER FERRULE A/F HEX



	OBSOLETE	OBSOLETE	OBSOLETE		OBSOLETE		OBSOLETE
1	1	1	1	1	1	1	1
1	1	1	1	1	1	1	1
5	75	65	55	45	35	25	15
QUANTITY PER ASSY							
PARTS LIST							

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANSON MA	14FEB09	TE Connectivity			
		CHK RITA ZUO	14FEB09				
		APVD BOB ZHAO	14FEB09				
		PRODUCT SPEC 108-112000					
		APPLICATION SPEC		F TYPE STRAIGHT PLUG HEX CRIMP			
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE TABLE		-		WEIGHT	A300779	C-1814821	-
CUSTOMER DRAWING				SCALE	NTS	SHEET	1 OF 1
						REV	C2