


MINIATURE PCB RELAY OJ/OJE

INTRODUCTION

TE Connectivity (TE)'s Miniature Power PCB Relays OJ & OJE is general purpose relay designed for various types of loads (e.g., resistive, inductive) with compact size. The relay is designed as 1 form A contact arrangement with different contact rating current from 3A to 10A, also sensitive coil, WG version and Haz-Loc version are available.

FEATURES

- 1 Pole, 1 Form A (NO) Contact
- 3-10A contact rating
- Small size with outline dimension of 18.2L*10.2W*14.7H(mm)
- 4000Vrms coil contact di-electric strength (OJ type)
- Sensitive coil optional (200mW type);
- WG version, Anti-Ex version (Haz-Loc version) optional



APPLICATIONS

- Major home appliances
- Small appliances
- HVAC
- Industrial control

APPROVALS

- VDE 40007630
- cULus E82292
- CQC03001007764
- TUV R 501391660014-0015



MINIATURE PCB RELAY OJ/OJE

CONTACT DATA

Contact arrangement	1 form A, 1 NO
Rated voltage	30VDC, 250VAC
Max. switching voltage	30VDC, 277VAC
Rated current	3 to 10A
Contact material	AgNi, AgSnO, AgCdO
Initial contact resistance	100 milliohms @ 1A, 6VDC
Minimum recommended contact load	100mA, 5VDC
Operate time max.	OJ/OJE-L: 15ms
	OJ/OJE-D/H: 10ms
Release time max.	4ms

ELECTRICAL ENDURANCE

UL	
OJ/OJE-LM	3A 250VAC, general use, 100k ops
OJ/OJE-DM	5A 250VAC 85°C 60k ops, 10 LRA / 1.5 FLA, 120VAC, 100k ops
OJ/OJE-LMH	8A 277VAC res, 70°C 100k ops (SS), 6.6 LRA / 1.1 FLA, 120VAC, 105°C 100k ops
OJ/OJE-LMH2	8A 250VAC res, 85°C 30k ops, 12 LRA / 2 FLA 250VAC, 85°C 100k ops
OJ/OJE-HM	10A 250VAC, general use, 30k ops (SH type), 18 LRA / 4 FLA, 240VAC, 85°C 100k ops, 7.5A 240VAC res, 105°C 100k ops (SS)
OJ/OJE-HM2	10A 250VAC res, 100k ops (SS type), 7.5A 240VAC res, 105°C 100k ops (SS type)
OJ/OJE-HM6	10A 250VAC res, 85°C 50k ops (OJ WG type only), 7.5A 240VAC res, 105°C 100k ops
VDE	
OJ/OJE-LM	3A 250VAC res, 55°C 100k ops
OJE-DM	5A 250VAC res, 85°C 50k ops
OJ/OJE-LMH	8A 250VAC res, 85°C 10k ops
OJ-LMH2	8A 250VAC res, 85°C 25k ops
OJ-LMH2	5A 250VAC res, 105°C 50k ops
OJE-HM	10A 250VAC res, 85°C 30k ops
OJ-HM	10A 250VAC res, 85°C 10k ops
OJ-HM2	10A 250VAC res, 85°C 50k ops
Mechanical endurance, DC coil	10x10 ⁶ operations

MINIATURE PCB RELAY OJ/OJE

COIL DATA

Coil voltage range	3 to 48VDC
Operative range, IEC 61810	2
Coil insulation system according UL	Class F

COIL VERSIONS, DC COIL, OJ/OJE-L SENSITIVE TYPE

Coil code	Rated voltage VDC	Operate voltage VDC	Release voltage VDC	Coil resistance $\Omega \pm 10\%$	Rated coil power mW
003	3	2.25	0.3	45	200
005	5	3.75	0.5	125	200
006	6	4.5	0.6	180	200
009	9	6.75	0.9	405	200
012	12	9	1.2	720	200
024	24	18	2.4	2880	200
036	36	27	3.6	6480	200
048	48	36	4.8	11520	200


All figures are given for coil without pre-energization, at ambient temperature +23°C

COIL VERSIONS, DC COIL, OJ/OJE-D&H SENSITIVE TYPE


Coil code	Rated voltage VDC	Operate voltage VDC	Release voltage VDC	Coil resistance $\Omega \pm 10\%$	Rated coil power mW
003	3	2.25	0.3	20	450
005	5	3.75	0.5	55.5	450
006	6	4.5	0.6	80	450
009	9	6.75	0.9	180	450
012	12	9	1.2	320	450
024	24	18	2.4	1280	450
036	36	27	3.6	2880	450
048	48	36	4.8	5120	450

All figures are given for coil without pre-energization, at ambient temperature +23°C


Electrical endurance



Operate time



Coil temperature rise



MINIATURE PCB RELAY OJ/OJE

INSULATION DATA


Initial dielectric strength	
Between open contacts	750Vrms
Between contact and coil	OJ: 4000Vrms
	OJE: 3000Vrms
Clearance/creepage	
Between contact and coil	OJ: > 7.7mm / 9.4mm
Between contact and coil	OJE: > 3.2mm / 3.6mm
Tracking index of relay base	PTI 250

OTHER DATA

Material compliance	EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customer-support/rohssupportcenter
Ambient temperature	
LM	-40 ~ +105C
DM	-40 ~ +85C
LMH(2)	-40 ~ +105C
HM(2)/HM6	-40 ~ +105C
Category of environmental protection	
IEC 61810	RTII - flux proof
	RTIII - wash tight
Shock resistance (functional)	10g
Shock resistance (destructive)	100g
Weight	6g
Resistance to soldering heat THT	
IEC 60068-2-20	RTII: 270°C/10s
	RTIII: 260°C/5s
Packaging unit	Tray/100, Carton box/1000


TERMINAL ASSIGNMENT

Bottom view on solder pins



PCB LAYOUT

Bottom view on solder pins



DIMENSIONS (Unit: mm)





Diagram dimension	Tolerance
0.99mm max.	±0.1 mm
1-2.9mm	±0.2 mm
3mm min.	±0.3 mm

MINIATURE PCB RELAY OJ/OJE

ORDERING INFORMATION



MINIATURE PCB RELAY OJ/OJE

PRODUCT INFORMATION

Product Code	Rating	Contact Material	Coil voltage	Coil powder	Type	Insulation	Enclosure	Part Number	
OJE-SH-112LM,000	3 A	AgNi	12 VDC	200 mW	Standard	Class F	Wash tight	1461401-5	
OJ-SS-112LM,000			Flux proof				2-1419129-1		
OJ-SS-124LM,000							3-1419129-1		
OJE-SS-112LM,000							4-1419128-6		
OJ-SH-105LM,000							Wash tight	1461404-1	
OJ-SH-112LM,000			1461404-6						
OJE-SH-112DM,00EOW	5 A		450 mW	EX-version		Flux proof	2071369-1		
OJE-SH-105DM,000				Standard			1461400-1		
OJE-SS-112DM,000							4-1419128-2		
OJE-SH-124DM,000				Wash tight			1461400-5		
OJ-SH-112DM,000						1461406-4			
OJ-SH-105LMH,000						8-1419128-1			
OJ-SH-112LMH,000	8 A	AgCdO	12 VDC	200 mW			9-1419128-8		
OJ-SS-112LMH2			AgSnO					WG version	Flux proof
OJ-SS-112LMH2-WG		1721874-5							
OJ-SS-124LMH2		24 VDC	standard				1721260-6		
OJE-SH-105LMH,000		AgCdO	5 VDC				Wash tight	1461403-3	
OJE-SH-112LMH,000			12 VDC					1461403-4	
OJE-SS-112LMH2	AgSnO			Flux proof	1721261-5				
OJE-SH-105HM,000	10 A	AgCdO	5 VDC	450 mW			Wash tight	1461402-4	
OJE-SH-112HM,000			12 VDC				1461402-6		
OJE-SS-112HM2,000		AgSnO						Flux proof	1721539-5
OJE-SS-112HM2.000TO									1-1721539-7
OJE-SS-112HMF,F000		AgCdO							4-1419128-4
OJE-SS-124HMF,F000									24 VDC
OJ-SS-112HM6-WG,00000	AgSnO		12 VDC	WG version		2071398-1			
OJ-SS-124HM2,000			24 VDC	standard	1721538-7				
OJE-SH-112HMF,00EOW		AgCdO	12 VDC		EX-version		Wash tight	2071370-1	
OJ-SS-112LMH2-WEX1,00000	8 A	AgSnO		200 mW	EX-version + WG		Flux proof	2071404-1	
OJ-SH-112HM2-WG,00000	10 A		12 V	450 mW	WG version		Wash tight	2071505-1	

te.com

©2025 TE Connectivity plc. Family of Companies. All Rights Reserved.

ALCOSWITCH, TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks owned or licensed by the TE Connectivity plc. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

03/25 ED