







RECOMMENDED PANEL CUTOUT EMPFOHLENER FRONTPLATTEN AUSSCHNITT



NOTE 1: WITHOUT REAR SHIELD TAB (X)

NOTE 2: SIDE GROUND TAB REAR OF PEG 3.05 mm (R)

NOTE 3: PANEL GROUND FLANGES BOTH SIDES AND TOP (GF5)

NOTE 4: MODIFIED SHIELD

NOTE 5: RoHS COMPLIANT

MATERIALS AND FINISH

HOUSING: GLASS FILLED POLYESTER UL 94 V-0 BLACK

SHIELDING: Cu ALLOY, PLATED WITH Ni

CONTACTS: PHOSPHOR BRONZE

CONTACT FINISH: Au, 0.8 µm (30 µin) OVER Ni

TERMINAL FINISH: Sn MATTE

LED LENS: EPOXY

OPERATING TEMPERATURE: 0°C TO 70°C


NO. IDENT.-NR.	LED 2 LEFT LED 2 LINKS	LED 1 RIGHT LED 1 RECHTS	LED CODE
203400	YELLOW	GREEN	L1
203488	ORANGE/GREEN	ORANGE/GREEN	L9

Copyright by ERNI GmbH
Proper use and notice pursuant to ISO 10116 is to be observed.

Information: SCHEMATIC NUMBER: M5B01			Tolerances		 All Dimensions in mm [in]		Scale 2:1				
All rights reserved. Only for Information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.			Subject to modification without prior notice. Drawing will not be updated.			Designation					
						MOD JACK - MJIM 8C10T, 1x2, INT. MAG., LED ALIGNED					
			A		05.02.2007				www.ERNI.com		203494
Index		Date						Class		MJIM	
										A3	

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16016 to be observed.

ELECTRICAL SCHEMATICS 1000 BASE T - M5B01
ELEKTRISCHER SCHALTPLAN



MAGNETICS SPECIFICATIONS @ 25°C

Turns Ratio: 1CT:1CT $\pm$ 3%

OCL(100 KHz, 0.1 V, 8 mA) 350 μ H MIN

Insertion Loss:

1-100 MHz -1.1 dB MAX

Return Loss:

1-40 MHz -18 dB MIN

60 MHz -14 dB MIN

80 MHz -12 dB MIN

100 MHz -10 dB MIN

Crosstalk:

1-100 MHz -35 dB TYP

CMR:

0.1 - 30 MHz -50 dB TYP


30 - 60 MHz -40 dB TYP

60 - 100 MHz -35 dB TYP

Isolation

1500 Vrms

RECOMMENDED PCB LAYOUT - COMPONENT SIDE VIEW
EMPFOHLENES LEITERPLATTEN-LAYOUT - BESTÜCKUNGSSEITE
ALL TOLERANCES $\pm$ 0.05 UNLESS NOTED



LED SPECIFICATIONS
LED ANWEISUNG

COLOR FARBE	V _f TYP	V _f MAX	I _f mA	CIRCUIT DIAGRAM SCHALTPLAN
YELLOW	2.1	2.5	20	
GREEN	2.2	2.5	20	
ORANGE/GREEN	2.05/2.2	2.5	20	

Copyright by ERNI GmbH.
Proprietary notice pursuant to ISO 16016 to be observed.

Information:	Tolerances		Scale 2:1
All rights reserved. Only for Information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.	Subject to modification without prior notice. Drawing will not be updated.	Designation MOD JACK - MJIM 8C10T, 1x2, INT. MAG., LED ALIGNED	
	www.ERNI.com	203494	I (2/2) A3
		Class	MJIM