





SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED		NO MISSING SYMBOL NUMBER	
	LAST NO. USED			
	17			
	11			

DWS STATUS				ZONE				REVISION HISTORY				AUTH		DR	APVD	APVD
DATE	STG	REV	N/P	CHG												
28MR12	R	01	-	-				ALL PARTS - RELEASED				414208	JMR	JMR	JRM	
02AP12	R	02	-	-				ALL PARTS - UPDATED PDM ATTRIBUTES 13877090 & 13886440 - 1.7 -2.12 CABLE DIA WAS 1.7 -1.9				417668	JTV	JTV	JRM	
13MR23	R	03	-	-				35760365, 35760087 - RELEASED				559830	AHY	JAA	JPS	
31MY23	R	04	-	-				35760087 - UPDATED PART AVAILABILITY (P/N WAS NOT AVAILABLE)				560675	JAA	JAA	JPS	



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - RECOMMENDED MATING BLADE THICKNESS 0.6 ±0.015 mm
RECOMMENDED MATING BLADE WIDTH NOT TO EXCEED 1.3 mm.
 - DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
 - MAXIMUM CURRENT CAPACITY IS 12 AMPS WITH 0.8 mm² COPPER CABLE.
 - * DENOTES DIMENSIONS MADE AT CUT-OFF AND CRIMP DIE.
 - PLUS ANGLE IS WING BOTTOM SURFACE ROTATED COUNTERCLOCKWISE AGAINST THE BOX BOTTOM SURFACE.
 - PLATING TYPE:
 - REFLOW TIN 1.9 - 3.3 MICROMETERS THICK OVER COPPER UNDERPLATE 0.5 - 1 MICROMETERS THICK.
 - SELECTIVE SILVER 2 - 3 MICROMETERS THICK OVER NICKEL UNDERPLATE 0.13 - 0.51 MICROMETERS THICK AND EVABRITE.PLATING TYPE INFORMATION SHOWN ABOVE IS REFERENCE ONLY: PLATING REQUIREMENTS ARE CONTAINED IN APPLICABLE MATERIAL SPECIFICATION.

6 PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
FROM 0 TO 12	CHART C
TOLERANCE UNLESS OTHERWISE SPECIFIED	> 12
±0.1	±0.2
ANGULAR TOLERANCE ±2°	

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.	
DWS TYPE	
PART DRAWING	
STYLE	
VOLUME (CM ³)	
DISTR CODE	
D	
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE 2003 GLOBAL DIMENSIONS AND TOLERANCING ADDENDUM-2003. SEPARATE PATTERNING OF FEATURES MAY BE ORDERED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	
DO NOT SCALE	
USE MATH DATA	

• APTIV •	
CONNECTION SYSTEMS	
WARREN, OH	
COPYRIGHT 2012 APTIV, ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DR	DATE
APVD1 J. RAINEY	28MR12
APVD2 J. RAINEY	28MR12
APVD3 JOHN MORELLO	28MR12
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001	
MATERIAL SPEC CHART	
DRAWING NAME	
TAXI TERM F PERF PACK 1.2 SEALED	
DRAWING NUMBER	
13886441	
SIZE	SCALE
A0	20:1
FRAME NO	SHEET NO
1	1
STG	REV
04	-