



A Product Line of
Diodes Incorporated



PRODUCT SPECIFICATION

NOMINAL FREQUENCY	125.000000 MHz
PRODUCT TYPE	TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR
SPEC. NO. (P/N)	HX3AC5006Q
ISSUE DATE	April 17, 2023
VERSION	A

Diodes Incorporated

No.2, Ziqiang 5th Rd., Zhongli Industrial Park,
Zhongli Dist., Taoyuan City 32063, Taiwan (R.O.C.)
TEL: 886-3-451-8888
FAX: 886-3-461-3865
<https://www.diodes.com>

***Pb-free**
***RoHS Compliant**
***HF-Halogen Free**
***REACH Compliant**
***AEC-Q104 Compliant**
***MSL: Level 1**

TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

HX3AC5006Q

VER. A 17-Apr-23

VERSION HISTORY

[illegible]

TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

HX3AC5006Q

VER. A 17-Apr-23

ELECTRICAL SPECIFICATIONS

SRe Part Number : HX3AC5006Q

Item	Symbol	Specifications	Units	Notes
Nominal Frequency	Fo	125.000000	MHz	
Frequency Stability	FT	± 50	ppm	**See note
Operating Temperature Range	TR	-55 to +125	°C	
Supply Voltage	V _{DD}	+3.3 $\pm$ 10%	V	
Logic Type	LT	LVC MOS		
Supply Current, Output Enabled	I _{DD} /OE	26	mA	Max.
Supply Current, Output Disabled	I _{DD} /OD	10	μ A	Max.
Duty Cycle (Symmetry)	DC/SY	45 / 55	%	Measured 50% of Waveform
Rise / Fall Time	T _R /T _F	2	ns	Max. measured 20/80% of Waveform
Output Voltage "0" Level	V _{OL}	10% V _{DD}	V	Max.
Output Voltage "1" Level	V _{OH}	90% V _{DD}	V	Min.
Output Load	CL	15	pF	Max.
Jitter, Phase	RMS	0.3	ps	Max. 12KHz ~ 20MHz Frequency Band
Jitter, Accumulated	RMS(1- σ)	4	ps	Max. 20,000 Consecutive Periods
Jitter, Peak to Peak	Pk-Pk	40	ps	Max. 100,000 Random Periods
Start Up Time		2	ms	Max.
Storage Temperature Range		-55 to +125	°C	

****Stability includes all combinations of Operating Temperature, Load changes, rated Input (Supply) Voltage changes, Initial Calibration Tolerance (25°C), Aging (1 year at 25°C Average Effective Ambient Temperature), Shock and Vibration.**

Output Enable / Disable Function


Parameter	Min.	Typ.	Max.	Units	Notes
Input Voltage (Pin1), Output Enable	0.7V _{DD}			V	Or Open
Input Voltage (Pin1), Output Disable (low power standby)			0.3V _{DD}	V	Output is Hi-Z
Output Disable Delay			200	ns	
Output Enable Delay			1	ms	

TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR


HX3AC5006Q

VER. A 17-Apr-23

TEST CIRCUIT



OUTPUT WAVEFORM



AEC-Q104 RELIABILITY TEST SPECIFICATIONS:

1. Initial

1.1 Physical Dimensions: JESD22, Method JB1-100

1.2 External Visual: MIL-STD-883, Method 2009

1.3 Start Up and Temperature Steps: ISO 16750-4

2. Mechanical

2.1 Mechanical Shock: Customize (Test condition: 5,000g, 0.3ms, 1/2 sine)

2.2 Vibration: MIL-STD-202G Method 204D (Test condition : 20g, 10-2,000Hz swept sine)

2.3 Solderability: JEDEC, J-STD-002

2.4 Drop testing: JEDEC, JESD22-B111

3. Environmental

3.1 Temperature Cycle: JEDEC, JESD22-A104

3.2 Biased HAST: JEDEC, JESD22-A101

3.3 High Temperature Operating Life: JEDEC, JESD22-A108

3.4 High Temperature Storage Life: JEDEC, JESD22-A103

3.5 High Temperature & High Humidity: JEDEC, JESD22-A102


3.6 Low Temperature Storage Life: JEDEC, JESD22-A119

3.7 ESD Testing : JEDEC JS-001 / JEDEC JS-002

3.8 Latch up Testing : JESD78

SUGGESTED IR REFLOW PROFILE

*As per IPC-JEDEC J-STD-020D



Note:


	Stage	Temperature	Time
A	Preheat	150~200°C	60~120 Sec
B	Primary Heat	217°C	60~150 Sec
C	Peak	260°C	10 Sec

TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR


HX3AC5006Q

VER. A 17-Apr-23


MARKING




MECHANICAL DRAWINGS (Scale: None. Dimensions are in mm.)



Recommended Land Pattern*



*External high-frequency power decoupling is recommended.(see test circuit for minimum recommendation). To ensure optimal performance, do not route traces beneath the package.



(Bottom View)


Pin	Function
1	OE
2	Ground
3	Clock Output
4	V _{DD}

TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

HX3AC5006Q

VER. A 17-Apr-23

TAPE&REEL



1. 230mm minimum leader which consist of carrier and/or tape followed by a minimum of 160mm of empty carrier tape sealed with cover tape.
2. 160mm minimum trailer of empty carrier tape sealed with cover tape.

TYPE HX 3.2x2.5 SEAM SEALED CRYSTAL CLOCK OSCILLATOR

HX3AC5006Q

VER. A 17-Apr-23

PACKING

