

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

BY -

ALL RIGHTS RESERVED.

LOC
H


DIST
-

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	AI	ECR-17-008413	12JUN2017	T.Z	H.W

NOTES:

- 1 PN. AS SHOWN 2173014-1.
2 MARKING: P=PRODUCTION LOCATION, Y=YEAR, WW=WEEK, D=DAY, LL=PRODUCTION LINE, S=SHIFT
3 RECOMMENDED PWB LAYOUT SEE SHEET 2
4 PACKAGING IN EIA 481-D SEE SHEET 3
5 NUMBER OF PRODUCTS ON REEL/IN BOX SEE SHEET 3
6 MAX WORKING RANGE 0.50 MM (SEE ALSO SHEET 2) WITH Fmin=0.20N
7 ADD ALTERNATIVE MATERIAL TO SECURE SUPPLY CHAIN.



SCALE 5:2



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

PACKAGING QUANTITY

PCS/REEL	REEL/BOX	PCS/BOX
750	8	6000

USER DIRECTION OF UNREELING

Ø 1,5 (G01)

20,0±0,1 (G02)

4,0±0,1 (G03)

2,0 (G04)

1,75±0,10 (G05)

(G07)

(G08)

(G09)

(G10)

(G11)

(G12)

(G13)

(G14)

(G15)

(G16)

(G17)

(G18)

(G19)

(G20)

(G21)

(G22)

(G23)

(G24)

(G25)

(G26)

(G27)

(G28)

(G29)

(G30)

(G31)

(G32)

(G33)

(G34)

(G35)

(G36)

(G37)

(G38)

(G39)

(G40)

TRAILER SECTION:
=> 10 EMPTY POCKETS

COMPONENT SECTION:
750 PCS

LEADER SECTION:
=>10 EMPTY POCKETS

0,40 (H03)

2,0 (H01)

6,8 (H02)

14,0 (H06)

3,7 (H04)


5,7 (H05)

SECTION A - A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.1
2 PLC ±0.05
3 PLC ±0.025
4 PLC ±0.01
ANGLES ±2

MATERIAL

-

FINISH

-

DWN 12nov2010

M.Gosselink

CHK 12nov2010

M.Gosselink

APVD 12nov2010

D.Halberstadt

PRODUCT SPEC

108-19423

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

3.5mm AV connector,
compressive, chamfered

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-2173014

RESTRICTED TO

-

SCALE

5

SHEET

3

OF

3

REV

A1