







PERFORMANCE CHARACTERISTICS

CURRENT RATING 1.5 A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE 500V AC (CONT / CONT)
OPERATING TEMPERATURE -55°C TO 125°C
CONTACT RESISTANCE 20 MΩ MAX
INSERTION FORCE 0.75 N MAX /CONT
EXTRACTION FORCE 0.15 N MIN /CONT
INSULATION RESISTANCE 10⁴ MΩ MIN

NOTES

- LEAD FREE INDICATOR : LF- LEAD FREE
- PERFORMANCE LEVEL INDICATOR
(REF DWG No. BS,C,201844,003)
- THIS PRODUCT IS CSA APPROVED
THIS PRODUCT IS UL RECOGNISED
- FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING: BS4,201,572001
- THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVE
AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.



Material				Spec ref			
Mat code				✓			
Heat treat				TOLERANCE H/2 TO DEC A/2 L1 TO H/2			
Plating/Finish				projection			
Dr 27 08 96				MM			
W.Panis				size			
Eng				Scale			
Dr				Product Family			
Appr				Model Name			
-				Model Revision			
-				REL Level			
-				MPACS 5+2R RA RCP			
-				CONN TYPE A			
BS, C, 201444, 018				Rev.			
C				CUSTOMER DRAWING			
sheet 1 of 1				Printed: Apr 19, 2008			