

EMP Protector 3401.99.0020

Description

GDT technology up to 1.0 GHz

Benefits

DC continuity for remote powering
The protector can also be installed reversely
GDT holder with chain
Replaceable GDT 9071.99.0547 (230 V) included
Compliant to IEC 61643-21



Product Configuration

Main path connectors	Port 1: <u>unprotected</u> , F jack (female) - Port 2: <u>protected</u> , F jack (female)
Mounting and grounding	MH12 (bulkhead mounting), brk (bracket)
Side of bulkhead	protected side

Technical Data

Electrical Data

Impedance	75 Ω
Frequency range	0 - 1000 MHz
Insertion loss	≤ 0.2 dB
RF CW power	≤ 50 W
PIM 3rd order	not specified

Surge current handling capability	40 single / 20 kA multiple kA (test pulse 8/20 μ s)
Residual pulse energy	350 μ J typically (test pulse 4 kV 1.2/50 μ s / 2 kA 8/20 μ s) main path - protected side

Mechanical Data

Number of matings	100
Weight	103 g

Environmental Data

Operating temperature	-40 °C to +85 °C
Waterproof degree	IP65 (according to IEC 60529, data refer to the coupled state)
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Housing	Brass	SUCOPLATE (R) Plating
Port 1 center contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Port 2 center contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing	DOU-00003989.1
Mounting instruction	DOC-0000176104