



P14 Rapid-2_5


Capacitive Humidity Sensor

New version with outstanding response time – Optimal for weather balloons and radiosondes

Benefits & Characteristics

- Extraordinary fast response time: 3 x faster than P14 Rapid
- Fast recovery time after condensation
- Temperature shock resistant
- High humidity stability
- Wide temperature range

Illustration¹⁾



1) For actual size, see dimensions

Technical Data - Preliminary


Dimensions (L x W x H / H2 in mm):	5.0 x 3.81 x 0.4 / 0.8
Capacitance at 30 % RH and +23 °C (C ₃₀):*	650 pF ±150 pF
Typical sensitivity (C ₃₀ = 650 pF, 15 % RH to 90 % RH):	1.1 pF/% RH
Operating humidity range:	0 % RH to 100 % RH (maximal dew point: +85 °C)
Operating temperature range:	-80 °C to +150 °C
Loss factor:	< 0.05 (at 23 °C, at 10 kHz, at 15 % RH to 90 % RH)
Linearity error:	< 1.5 % RH (15 % RH to 90 % RH at +23 °C after one-point calibration)
Hysteresis:	< 1.5 % RH
Response time t ₆₃ : ²⁾	0.3 s ± 0.2 s (50 % RH to 0 % RH at +23 °C)
2) The response time is often measured for increasing humidity steps, whereas physics predicts that decreasing humidity leads to generally far longer response times for capacitive humidity sensors. IST thus measures response times always for decreasing humidity values, since this is the worst case.	
Temperature dependence (nominal):	$\Delta \% RH = (B1 \times \% RH + B2) \times T [^{\circ}C] + (B3 \times \% RH + B4)$ $B1 = 0.0014 [1/^{\circ}C]$ $B2 = 0.1325 [\% RH/^{\circ}C]$ $B3 = -0.0317$ $B4 = -3.0876 [\% RH]$
Measurement frequency:	1 kHz to 100 kHz (recommended 10 kHz)
Maximal supply voltage:	< 12 V _{pp} AC
Signal form:	alternating signal without DC bias




Connection:* Au/Cu-wire, Ø 0.4 mm
Packaging: packed in a blister of 5 pcs
* Customer-specific alternatives available

The calibration of the sensor must be done 5 days after soldering at the earliest.

Response Time (typical)




Characteristic Curve (typical)





Product Photo



Order Information - Au/Cu-wire, Ø 0.4 mm

Order code	P14 Rapid-2_5 (650±150 pF)
Mouser Product number	153415
	916-15345



Innovative Sensor Technology IST AG, Stegrütistrasse 14, 9642 Ebnat-Kappel, Switzerland
Phone: +41 71 992 01 00 | Fax: +41 71 992 01 99 | Email: info@ist-ag.com | www.ist-ag.com

All mechanical dimensions are valid at 25 °C ambient temperature, if not differently indicated • All data except the mechanical dimensions only have information purposes and are not to be understood as assured characteristics • Technical changes without previous announcement as well as mistakes reserved • The information on this data sheet was examined carefully and will be accepted as correct; No liability in case of mistakes • Load with extreme values during a longer period can affect the reliability • The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner • Typing errors and mistakes reserved • Product specifications are subject to change without notice • All rights reserved