





Features

- 1920x1080@30fps
- HDR
- Lens D/H/V FOV:67°/55°/42°
- OS Support: Windows, Linux, Android, MacOS (UVC)
- Compliant to USB2.0 and USB Video Class
- Complies with CE/FCC Class A



Mechanical Drawing

Mechanical Drawing



Lens Specification

Lens FOV:
Vertical:42.7°
Horizontal:69.9°
Diagonal:77.3°
Composition:4P
IRCF:650nm



Headquarters (Taiwan)

5F., No. 237, Sec. 1, Datong Rd.,
Xizhi Dist., New Taipei City 221,
Taiwan
Tel: +886-2-7703-3000
Email: sales@innodisk.com

Branch Offices:

USA

usasales@innodisk.com
+1-510-770-9421

Europe

eusales@innodisk.com
+31-40-3045-400

Japan

jpsales@innodisk.com
+81-3-6667-0161

China

sales_cn@innodisk.com
+86-755-2167-3689

www.innodisk.com

© 2019 Innodisk Corporation.
All right reserved. Specifications
are subject to change without
prior notice.

December 2, 2022

Specifications

Resolution	1920x1080 @ 30fps
Output I/F	USB2.0
Power consumption	Approximate 1W
Dimension (WxLxH)	60 x 8 x 4.8 mm
Operating Temp.	-20°C ~ +70°C
Sensor Size	1/6"
Pixel Size	1.4 um
Lens type	Fixed focus (M5)
Lens D/H/V FOV	67°/55°/42°
OS Support	Windows, Linux, Android, MacOS

Order information

EV2U-RMR1-UMCB-C1

USB2.0 Fixed Focus Camera Module

7W2000000160

USB2.0 cable 1 meter, 5 pins, pitch 1mm

Cable appearance



www.innodisk.com