






REV.	DESCRIPTION/ECO NO.	DATE
	RELEASED	3/10/03
A	DIM. CHANGE	3/27/03
B	RoHS COMPLIANCE	5/9/06
C	CHNG. COMPONENT LAYOUT	3/21/17
D	ADD BOARD DIMENSIONS	8/28/17
E	ADD PHOTO	1/15/21




JKL PART NO.: BXA-12529
*RoHS COMPLIANCE

METRIC THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.3 2 PL +/- 0.2 ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE 12 V DUAL CCFL POWER SUPPLY			
DRAWN BY L. WENGSTROM	APPV'D BY S.N. 1/15/21	DATE 1/15/21	SIZE A	FSCM NO. 55335	DRAWING NO. BXA-12529		
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE	RELEASED DATE 3/10/03	REVISION DATE 1/15/21	REV. NO. E	SHEET 1 OF 2



BOARD PIN #	INPUT
1	+V (V in)
2	V (GND)
3	OUT 1
4	OUT2
5	OUT (GND)



CHARACTERISTICS	MIN	TYP	MAX
INPUT VOLTAGE: (vdc)	10.8	12.0	13.2
INPUT CURRENT: (mA)	220	260	500
OUTPUT VOLTAGE: (Vrms)	950	1000	1050
OUTPUT CURRENT (mA) x 2	4.5	5.5	6.5
OUTPUT FREQUENCY: (kHz)	25	35	45
OPERATING TEMP: (CELSIUS)	0	25	50

METRIC THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.3 2 PL +/- 0		JKL COMPONENTS CORPORATION			
	TITLE 12 V DUAL CCFL POWER SUPPLY		DRAWING NO. BXA-12529			
DRAWN BY L. WENGSTROM	APPV'D BY S.N. 1/15/21	DATE 1/15/21	SIZE A	FSCM NO. 55335	RELEASED DATE 3/10/03	
- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE NONE	REVISION DATE 1/15/21	REV. NO. E	SHEET 2 OF 2