







P. C. B LAYOUT (REFERENCE)
基板レイアウト(参考)

THICKNESS: $t1.6 \pm 0.2$
基板厚: $t1.6 \pm 0.2$

NOTE1. THE RECOMMENDED TAPPING SCREW IS SPECIFIED IN
JIS B 1122 2ND GRADE 2.6×8 AND P-TIGHT SCREW 2.6×8.
NOTE2. MATERIAL CODE APPEARS IN RAISED LETTERS.
NOTE3. MOLDING LOT (YEAR AND MONTH) APPEARS IN RAISED LETTERS.
NOTE4. COMPANY LOGO "JAE" & CAVITY NUMBER APPEARS IN RAISED
LETTERS.
NOTE5. THE ASSEMBLY LOT NUMBER IS INDICATED.
NOTE6. TERMINAL NUMBER APPEARS IN RAISED LETTERS.

注1. 推奨タッピングねじは、JIS B 1122 2種 2.6×8及び
Pタイトねじ2.6×8。
注2. 材料名を浮き出す。
注3. ハウジングの成形ロット(年月)を浮き出す。
注4. 社標、キャビティ番号を浮き出す。
注5. 組立、ロット番号を表記する。
注6. 端子番号を浮き出す。

7	060 TERMINAL-3	2	COPPER ALLOY	TIN PLATING	—
6	060 TERMINAL-2	6	COPPER ALLOY	TIN PLATING	—
5	060 TERMINAL-1	6	COPPER ALLOY	TIN PLATING	—
4	025 TERMINAL-3	4	BRASS	TIN PLATING	—
3	025 TERMINAL-2	2	BRASS	TIN PLATING	—
2	025 TERMINAL-1	4	BRASS	TIN PLATING	—
1	HOUSING	1	SPS-GF30	—	COLOR: GRAY
符号 NO	名 称 DESCRIPTION	個 数 QTY	材 料 MATERIAL	仕 上 FINISH	備 考 REMARKS

仕様書 (SPECIFICATION)		第1版 (ORIGINAL DATE)		尺度 (SCALE)		シリーズ (SERIES)		日本航空電子工業株式会社		SIZE A2
JACS-10940 JAHL-10940		03/OCT/2012		2:1		MX58				
公差 (GENERAL TOLERANCE)		製図 DR.		名称 (TITLE)		 JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.		図面番号 (DRAWING NO.)		版数 (REV.)
寸法 (DIMENSION)		担当 CHK.		MX58024NFA (MALE CONNECTOR)						
± 0.8 $\times \pm 0.4$ $\times \times \pm 0.1$ $\times \times \times \pm$		$\times^{\circ}$ $\pm$ $\times^{\circ} \times^{\circ}$ $\pm$		T. KINOSHITA Y. WATANABE A. OONO						
		承認 APPD.		質量 (MASS)		 13.3g 		SJ112378		2