









USB Series B Connector


156-2442-E

DIMENSIONS: mm

Date Last Revised:01/10/22



Section A-A



PCB Footprint: Receptacle (Thru-hole)

SPECIFICATIONS	
Rating:	1A/250VAC
Temperature:	-55°C to +85°C
Contact Resistance:	30 Milliohms Maximum Initial
Insulation Resistance:	1,000 M ohms Minimum
Dielectric Withstanding Voltage:	500 VAC
Capacitance:	2 Picofarads Maximum at 1KHZ
Insulator:	White Color
Recommended PC Board Thickness:	1.57mm
Recommended Panel Thickness:	2.67mm Maximum
RoHS Compliant	

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301511

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.