



3-WAY CONNECTORS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

MAXIMUM ELECTRICAL RATING: 75°C 600 VOLTS MAX.
INSULATION MATERIAL: VINYL
INSULATION COLOR:

 3WCV1: RED ■ 3WCV2: BLUE ■ 3WCV5: YELLOW ■
TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.	STUD SIZE		DIMENSION ^{inch} mm				FIGURE	Q'TY BOX
		d2		L	D	E	d1		
22-16 A.W.G. 0.5-1.5 mm ²	3WCN1	#8	.157 4.0	.472 12.0	.134 3.4	.189 4.8	.067 1.7		1000
16-14 A.W.G. 1.5-2.5 mm ²	3WCN2	#8	.157 4.0	.512 13.0	.161 4.1	.189 4.8	.091 2.3		1000
12-10 A.W.G. 4-6 mm ²	3WCN5	#8	.157 4.0	.591 15.0	.220 5.6	.236 6.0	.134 3.4		500
22-16 A.W.G. 0.5-1.5 mm ²	3WCV1	#8	.157 4.0	.669 17.0	.157 4.0	.394 10.0	.067 1.7		500
16-14 A.W.G. 1.5-2.5 mm ²	3WCV2	#8	.157 4.0	.709 18.0	.177 4.5	.394 10.0	.091 2.3		500
12-10 A.W.G. 4-6 mm ²	3WCV5	#8	.157 4.0	.886 22.0	.248 6.3	.512 13.0	.134 3.4		250



4-WAY CONNECTORS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

MAXIMUM ELECTRICAL RATING: 75°C 600 VOLTS MAX.
INSULATION MATERIAL: VINYL
INSULATION COLOR:

 4WCV1: RED ■ 4WCV2: BLUE ■

 4WCV5: YELLOW ■
TERMINAL MATERIAL: COPPER


WIRE RANGE A.W.G. mm ²	ITEM NO.	STUD SIZE		DIMENSION ^{inch} mm				FIGURE	Q'TY BOX
		d2		L	D	E	d1		
22-16 A.W.G. 0.5-1.5 mm ²	4WCN1	#8	.157 4.0	.945 24.0	.134 3.4	.189 4.8	.067 1.7		500
16-14 A.W.G. 1.5-2.5 mm ²	4WCN2	#8	.157 4.0	1.004 25.5	.161 4.1	.189 4.8	.091 2.3		500
12-10 A.W.G. 4-6 mm ²	4WCN5	#8	.157 4.0	1.181 30.0	.220 5.6	.236 6.0	.134 3.4		250
22-16 A.W.G. 0.5-1.5 mm ²	4WCV1	#8	.157 4.0	1.339 34.0	.157 4.0	.394 10.0	.067 1.7		250
16-14 A.W.G. 1.5-2.5 mm ²	4WCV2	#8	.157 4.0	1.398 35.5	.177 4.5	.394 10.0	.091 2.3		250
12-10 A.W.G. 4-6 mm ²	4WCV5	#8	.157 4.0	1.713 43.5	.248 6.3	.512 13.0	.134 3.4		200