

VINYL-INSULATED FORK TERMINALS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10	8
AMP.	9	12	17	18	30	35	50	70

MAXIMUM ELECTRICAL RATING: 75°C 600 VOLTS MAX.


INSULATION MATERIAL: VINYL

INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

8 A.W.G.: RED

TERMINAL MATERIAL: COPPER



WIRE RANGE A.W.G. mm ²	ITEM NO.		STUD SIZE		DIMENSION inch mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	d2		W	F	L	E	D	d1	T		
22-16 A.W.G. 0.5-1.5 mm ²	AVB1-3.2	AV1-3.2	#4	.126 3.2	.217 5.5	.197 5.0	.654 16.6	.394 10.0	.157 4.0	.067 1.7	.030 0.75	IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000
	AVB1-3.7	AV1-3.7	#6	.146 3.7	.260 6.6	.248 6.3	.728 18.5						1000
	AVB1-4	AV1-4	#8	.169 4.3	.315 8.0	.276 7.0	.780 19.8						1000
	AVB1-5	AV1-5	#10	.209 5.3			.764 19.4						1000
	AVB1-6	AV1-6	1/4	.252 6.4	.457 11.6	.433 11.0	.996 25.3						1000
	AVB1-8	AV1-8	5/16	.331 8.4			.961 24.4						1000
	AVB1-10	AV1-10	3/8	.413 10.5	.591 15.0	.496 12.6	1.083 27.5						1000
16-14 A.W.G. 1.5-2.5 mm ²	AVB2-3.2	AV2-3.2	#4	.126 3.2	.260 6.6	.185 4.7	.669 17.0	.394 10.0	.177 4.5	.091 2.3	.031 0.8	IZUMI MODEL 34 WITH DIE INDEX COLOR:BLUE OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLUE	1000
	AVB2-3.7	AV2-3.7	#6	.146 3.7		.248 6.3	.728 18.5						1000
	AVB2-4	AV2-4	#8	.169 4.3	.335 8.5	.272 6.9	.823 20.9						1000
	AVB2-5	AV2-5	#10	.209 5.3	.374 9.5	.287 7.3	.811 20.6						1000
	AVB2-6	AV2-6	1/4	.252 6.4	.472 12.0	.433 11.0	1.004 25.5						1000
	AVB2-8	AV2-8	5/16	.331 8.4			.972 24.7						1000
	AVB2-10	AV2-10	3/8	.413 10.5	.591 15.0	.496 12.6	1.083 27.5						1000
12-10 A.W.G. 4-6 mm ²	AVB5-4	AV5-4	#8	.169 4.3	.283 7.2	.228 5.8	.839 21.3	.512 13.0	.252 6.4	.134 3.4	.039 1.0	IZUMI MODEL 5 WITH DIE INDEX COLOR:YELLOW OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:YELLOW	500
	AVB5-5	AV5-5	#10	.209 5.3	.374 9.5	.358 9.1	1.008 25.6						500
	AVB5-6	AV5-6	1/4	.252 6.4	.472 12.0	.413 10.5	1.110 28.2						500
	AVB5-8	AV5-8	5/16	.331 8.4	.591 15.0	.531 13.5	1.276 32.4						500
	AVB5-10	AV5-10	3/8	.413 10.5			1.240 31.5						500
	AVB5-12	AV5-12	1/2	.512 13.0	.756 19.2	.630 16.0	1.421 36.1						500
8 A.W.G. mm ²	AVB8-4	AV8-4	#8	.169 4.3	.315 8.0	.366 9.3	1.130 28.7	.657 16.7	.335 8.5	.177 4.5	.047 1.2		500

UL cUL ALL LISTED