


NON-INSULATED PARALLEL & BUTT CONNECTORS



MAXIMUM ELECTRIC CURRENT:

A.W.G.	26	24	22	20	18	16	14	12	10	8
AMP.	5.5	7	9	12	17	18	30	35	50	70

TERMINAL MATERIAL: COPPER TUBULAR

WIRE RANGE A.W.G. mm ²	ITEM NO.			DIMENSION inch mm				CRIMPING TOOL	Q'TY BOX
	PARALLEL	L	BUTT	L	D	d1	T		
26-22 A.W.G. 0.2-0.5 mm ²	PNT0.5	.197 5.0	BNT0.5	.472 12.0	.083 2.1	.051 1.3	.016 0.4	K.S. MODEL KSTHT-203 WITH DIE INDEX NO:(INSUL)16-22	1000
22-16 A.W.G. 0.5-1.5 mm ²	PNT1	.315 8.0	BNT1	.591 15.0	.130 3.3	.067 1.7	.031 0.8	IZUMI MODEL 5N18 WITH DIE INDEX NO:1.25 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO:22-18	1000
			BNT1-16	.630 16.0					1000
16-14 A.W.G. 1.5-2.5 mm ²	PNT2	.315 8.0	BNT2	.591 15.0	.154 3.9	.091 2.3	.031 0.8	IZUMI MODEL 5N18 WITH DIE INDEX NO:2 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO:16-14	1000
	PNT2-7	.276 7.0							
	PNT2-15	.591 15.0	BNT2-16	.630 16.0					
14-12 A.W.G. 2.5-4 mm ²	PNT3	.335 8.5	BNT3	.591 15.0	.197 5.0	.118 3.0	.039 1.0	IZUMI MODEL 5N18 WITH DIE INDEX NO:5.5 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO:12-10	1000
12-10 A.W.G. 4-6 mm ²	PNT5	.335 8.5	BNT5	.591 15.0	.213 5.4	.134 3.4	.039 1.0	IZUMI MODEL 5N18 WITH DIE INDEX NO:5.5 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO:12-10	1000
			BNT5-20	.787 20.0					
	PNT5-15	.335 15.0	BNT5-21	.827 21.0					
			BNT5-30	1.181 30.0					
8 A.W.G. 8 mm ²	PNT8	.374 9.5	BNT8	.827 21.0	.276 7.0	.181 4.6	.047 1.2	IZUMI MODEL 5N18 12#A WITH DIE INDEX NO:1.8 OR K.S. MODEL KST2000D-1322 WITH DIE INDEX NO:8	1000/500
			BNT8-42	1.654 42.0					250

UL cUL ALL LISTED