


VINYL-INSULATED DOUBLE CRIMP BUTT SPLICE CONNECTORS


MAXIMUM ELECTRIC CURRENT:


A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

MAXIMUM ELECTRICAL RATING: 75°C 600 VOLTS MAX.
CONNECTOR MATERIAL: COPPER INSULATION MATERIAL: VINYL
DOUBLE CRIMP: WITH COPPER SLEEVE ON BARREL
INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION ^{inch} mm			MATERIAL	CRIMPING TOOL	Q'TY BOX
		L	D	d1			
22-16 A.W.G. 0.5-1.5 mm ²	BVD1	1.043 26.5	.177 4.5	.071 1.8	COPPER PLATE	K.S. MODEL KST2000B WITH DIE INDEX COLOR:RED	1000
16-14 A.W.G. 1.5-2.5 mm ²	BVD2	1.083 27.5	.205 5.2	.098 2.5	COPPER PLATE	K.S. MODEL KST2000B WITH DIE INDEX COLOR:BLUE	1000
12-10 A.W.G. 4-6 mm ²	BVD5	1.240 31.5	.276 7.0	.134 3.4	COPPER PLATE	K.S. MODEL KST2000B WITH DIE INDEX COLOR:YELLOW	500

NYLON-INSULATED DOUBLE CRIMP BUTT SPLICE CONNECTORS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
CONNECTOR MATERIAL: COPPER INSULATION MATERIAL: NYLON
DOUBLE CRIMP: WITH COPPER SLEEVE ON BARREL
INSULATION COLOR:

22-16 A.W.G.: RED 16-14 A.W.G.: BLUE 12-10 A.W.G.: YELLOW

WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION ^{inch} mm			MATERIAL	CRIMPING TOOL	Q'TY BOX
		L	D	d1			
22-16 A.W.G. 0.5-1.5 mm ²	BNYDF1	1.024 26.0	.177 4.5	.067 1.8	COPPER PLATE	K.S. MODEL KST2000B WITH DIE INDEX COLOR:RED	1000
16-14 A.W.G. 1.5-2.5 mm ²	BNYDF2	1.063 27.0	.205 5.2	.098 2.5	COPPER PLATE	K.S. MODEL KST2000B WITH DIE INDEX COLOR:BLUE	1000
12-10 A.W.G. 4-6 mm ²	BNYDF5	1.233 31.3	.276 7.0	.142 3.6	COPPER PLATE	K.S. MODEL KST2000B WITH DIE INDEX COLOR:YELLOW	500



ALL LISTED

©: NOT UL AND C-UL LISTED