


VINYL-INSULATED (MOLDED EASY ENTRY) BLADE TERMINALS


MAXIMUM ELECTRIC CURRENT:

A.W.G.	22	20	18	16	14	12	10
AMP.	9	12	17	18	30	35	50

MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS MAX.
INSULATION MATERIAL: VINYL
INSULATION COLOR:

 22-16 A.W.G.: RED ■ 16-14 A.W.G.: BLUE ■ 12-10 A.W.G.: YELLOW ■
TERMINAL MATERIAL: COPPER

WIRE RANGE A.W.G. mm ²	ITEM NO.		DIMENSION inch mm							CRIMPING TOOL	Q'TY BOX
	BRAZED SEAM	BUTTED SEAM	W	F	L	E	D	d1	T		
22-16 A.W.G. 0.5-1.5 mm ²	DBVYB1-9	DBVY1-9	.110 2.8	.354 9.0	.780 19.8	.433 11.0	.157 4.0	.067 1.7	.030 0.75	IZUMI MODEL 34 WITH DIE INDEX COLOR:RED OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:RED	1000
	DBVYB1-10	DBVY1-10	.091 2.3	.394 10.0	.819 20.8						1000
	DBVYB1-11	DBVY1-11	.118 3.0	.433 11.0	.858 21.8						1000
	DBVYBS1-13	DBVYS1-13	.075 1.9	.512 13.0	.937 23.8						1000
	DBVYB1-13	DBVY1-13	.118 3.0								1000
	DBVYB1-14	DBVY1-14	.118 3.0	.551 14.0	.976 24.8						1000
	DBVYB1-18	DBVY1-18	.087 2.2	.709 18.0	1.134 28.8						1000
	DBVYBS1-18	DBVYS1-18	.079 2.0								1000
16-14 A.W.G. 1.5-2.5 mm ²	DBVYB2-9	DBVY2-9	.110 2.8	.354 9.0	.780 19.8	.433 11.0	.177 4.5	.091 2.3	.031 0.8	IZUMI MODEL 34 WITH DIE INDEX COLOR:BLUE OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:BLUE	1000
	DBVYB2-10	DBVY2-10	.094 2.4	.394 10.0	.819 20.8						1000
	DBVYB2-13	DBVY2-13	.094 2.4	.512 13.0	.937 23.8						1000
	DBVYBL2-13	DBVYL2-13	.118 3.0								1000
	DBVYB2-14	DBVY2-14	.094 2.4	.551 14.0	.976 24.8						1000
	DBVYBL2-14	DBVYL2-14	.118 3.0								1000
	DBVYBS2-18	DBVYS2-18	.079 2.0	.709 18.0	1.134 28.8						1000
	DBVYB2-18	DBVY2-18	.087 2.2								1000
	DBVYBL2-18	DBVYL2-18	.110 2.8								1000
12-10 A.W.G. 4-6 mm ²	DBVYB5-10	DBVY5-10	.110 2.8	.394 10.0	.906 23.0	.512 13.0	.252 6.4	.134 3.4	.039 1.0	IZUMI MODEL 5 WITH DIE INDEX COLOR:YELLOW OR K.S. MODEL KST2000A HRI-126J WITH DIE INDEX COLOR:YELLOW	500
	DBVYBS5-14	DBVYS5-14	.157 4.0	.551 14.0	1.063 27.0						500
	DBVYB5-14	DBVY5-14	.177 4.5								500
	DBVYBS5-18	DBVYS5-18	.079 2.0	.709 18.0	1.220 31.0						500
	DBVYB5-18	DBVY5-18	.177 4.5								500

UL cUL ALL LISTED