

CRIMP CONNECTORS

MAXIMUM ELECTRIC CURRENT:

A.W.G.	18	16	14	12	10	8
AMP.	17	18	30	35	50	70

LR: STANDARD CHEMICAL TREATMENT

LRR: FLASH






BS: PLATED BRASS

ZN: ZINC PLATED

TERMINAL MATERIAL:

ENACU1810LR: COPPER

ENAFE1810BS: STEEL

WIRE RANGE A.W.G. mm ²	ITEM NO.	DIMENSION inch mm				WIRE COMBINATIONS	CRIMPING TOOL	FIGURE	Q'TY BOX
		L	D	C	W				
18-10 A.W.G.	ENACU1810LRR	.374 9.5	.295 7.5	.205 5.2	.240 6.1	#10 X 2 2 + #12 X 3 2 + #14 X 5 4 + #16 X 7 8 + #18 X 10	K.S. MODEL KST5000A (18-10)		100
1.0-6.0 mm ²	ENAFE1810BS								
	ENAFE1810ZN								
14-8 A.W.G.	ENACU1408LRR	.610 15.5	.366 9.3	.264 6.7	.307 7.8	#8 X 2 2 + #10 X 3 3 + #12 X 5 #14 X 5 #12 X 3 w/1 or #14 X 2 or #16 X 2 or #18 X 2	K.S. MODEL KST5000A (14-8)		50
2.5-10 mm ²	ENAFE1408BS								
	ENAFE1408ZN								